

Digital position indicator

Size XS Stock

OP3DX
OP3SX

4 digit display

Stainless steel version available on request


- 4 digit display (9999) with red digits for tenths/hundredths
- Shaft driven position indicator
- Displays linear or angular movement by use of mechanism driven by a rotating shaft
- Nonflammable polycarbonate case Protection IP64
- Max. temperature 80°C
- Colour: orange
- Height of digits: 5mm
- Standard bore for shaft 14H7, smaller bores will require use of reducing sleeve



Gasket supplied



Clamp spacer OP3-BE




Options

- Version with stainless steel parts available
- Anti-rotation pin Ø6mm





Assembly

- Insert the indicator on to the shaft ensuring that the torque pin is inserted into the 5mm hole that should have been provided. Reset the display to zero and secure the fixing screw.

Shaft hole max. Ø14



OP3DX OP3SX



DISCOUNTS

Qty	1+	5+	+10
Disc.	List	-15%	On request

Part number	View	Pitch (mm)	Display after one turn (mm)	Max. speed (rpm)	Counting direction	Stock*	Price each 1 to 4
OP3-A10-DX	A	1	001 0	300	clockwise	✓	66,11 €
OP3-A20-DX	A	2	002 0	300	clockwise	✓	66,11 €
OP3-A40-DX	A	4	004 0	250	clockwise	✓	66,11 €
OP3-A50-DX	A	5	005 0	200	clockwise	✓	66,11 €
OP3-A100-DX	A	10	010 0	150	clockwise	✓	66,11 €
OP3-B10-DX	B	1	001 0	300	clockwise	✓	66,11 €
OP3-B20-DX	B	2	002 0	300	clockwise	✓	66,11 €
OP3-B40-DX	B	4	004 0	250	clockwise	✓	66,11 €
OP3-B50-DX	B	5	005 0	200	clockwise	-	66,11 €
OP3-B100-DX	B	10	010 0	150	clockwise	-	66,11 €
OP3-A10-SX	A	1	001 0	300	anticlockwise	✓	66,11 €
OP3-A20-SX	A	2	002 0	300	anticlockwise	-	66,11 €
OP3-A40-SX	A	4	004 0	250	anticlockwise	✓	66,11 €
OP3-A50-SX	A	5	005 0	200	anticlockwise	-	66,11 €
OP3-A100-SX	A	10	010 0	150	anticlockwise	✓	66,11 €
OP3-B10-SX	B	1	001 0	300	anticlockwise	-	66,11 €
OP3-B20-SX	B	2	002 0	300	anticlockwise	-	66,11 €
OP3-B40-SX	B	4	004 0	250	anticlockwise	-	66,11 €
OP3-B50-SX	B	5	005 0	200	anticlockwise	-	66,11 €
OP3-B100-SX	B	10	010 0	150	anticlockwise	-	66,11 €

*Depending on availability - Dimensions in mm

Our other products



CMM_SS

Male rod ends DIN ISO12240-4, Stainless steel / bronze - Economy range



RCX-6

Spherical tilt washer - DIN6319, concave



MDB_MTB

Moulded plastic bevel gear (nylon), 2:1



ZG0

Plastic spur gear, Machined plastic (delrin)



BOXKU

Boxed set of half round (Woodruff) keys NFE22179, Boxed set of half ...




PRF_GAL

Roller for aluminium profile, Hollow roller ø12



PW_PWG15

Worm - precision range, Stainless steel



H0

Crossed helical gear crossed axis at 90°, Machined plastic (delrin)



FF10

Offset spur gear reducer, from 0.78 to



CHM63-MOT

Asynchronous AC motorgearboxes 0.37



PRES5HR

Manual workbench press, Force up to



G-ECO

Eco range Spur gear, Steel C45

Complementary products



OP3_14_06

Reducing sleeve for OP indicators, Reduction socket



OPFL_OPMP

Numerical counter accessories, Locking clamp



LFM

Steel leadscrew, Medium carbon steel - 1 thread



VPRA_M

Handwheel with handle, Thermosetting plastic - galvanised steel hub