

# Manual bench press




## PRES7HR

## 700kg capacity

- **Knee-joint press**
- The maximum power is reached at the end of the stroke
- The travelling nut is prevented from turning
- Adjustable free height
- Screw stroke adjustment
- Quick and easy installation

### Uses

- This model is particularly robust and is normally used for the assembly of parts, simple bending tasks and various fastening operations



### DISCOUNTS

Qty	1+	2+
Disc.	List	On request

Part number	Power (kg)	Free height HL (mm)	Stroke length (mm)	Goose neck depth (mm)	Weight (kg)	Price each
PRES-7HR	700	35 - 260	40	95	25	955,42 €

Dimensions in mm

## Our other products




CLSCP\_SS  
Clevis components,  
short version,  
Stainless steel - short  
range



PM2  
Worm and wheel set,  
Machined plastic  
(delrin)



BOX-WM  
Box set of washer -  
DIN125, Box set of  
steel washers



RPPM  
RPP type belt per  
metre, RPP8 Steel  
cored polyurethane



PCS50SS  
Chain sprocket -  
Stainless steel,  
12.7mm (DIN 08B-1)




MDPOT  
Potentiometer,



PX  
Optional output shaft  
stainless steel, P  
gearboxes double  
sided outp...



BLHT30  
Right angled gearbox,  
from 1.65 to 4.40 Nm




QN  
Single row cylindrical  
roller bearing, Free  
outer ring



RFK28C  
Hypoid gearbox -  
Stainless steel, up to  
130 Nm



SSG2\_304L  
Stainless steel spur  
gear, Stainless steel  
304L



BPF  
Sheet steel flanged  
bearing for light  
loads, Sheet steel

## Complementary products



PRESSHR  
Manual workbench  
press, Force up to  
500kg



PRES4HR  
Manual workbench  
press, Force up to  
600kg



CDP  
Flanged drill bushing,  
Steel



CDPC  
Flanged drill bushing,  
Steel