

Profile assembly




- Suitable for loads up to 18000N
- Can be used to securely join all profile types
- Forms very efficient anti-twist joint
- Materials:
M8x50mm CHC screw: electroplated steel
Locking plate: electroplated steel

Uses

- For heavy or vibrating loads

Assembly

- Drill a stepped hole ($\varnothing 9$, $\varnothing 15$) at the required position
- Slide the screw locking plate in the slot
- Pass the end of the screw through the first profile (1), the locking plate and then into the central hole of the second profile (2) which was previously tapped ($M8 \times 25mm$) and tighten.



DISCOUNTS

Qty	1+	50+	100+
Disc.	List	-5%	On request

Part number	Load (N)	For profile	Tightening torque (Nm)	Weight (kg)	Stock*	Price each 1 to 49
PRF-FIX-STD	18000	All types of PRF profile	20	0,03	✓	2,10 €

*Depending on availability - Dimensions in mm

Our other products



CHAK
Hi-Klik TM indent
hinge, Hi-Klik™ -
Detent hinge



MSP23
Masterplate®
glueable insert Ø23,
Cylindrical Ø23 with
threaded s...



INS150
Self tapping insert
with collar-coarse
thread, With collar-
coarse t...



RPCTcss
Swivel castor with
central hole, Stainless
steel - Polyamide -
with ...



SUP
Self-centering
clamping hub steel,
Without locknut



ACL-FPA
Panel mounting block
for aluminium
structures, Angular
connector



H2
Crossed helical gear
crossed axis at 90°,
Steel 20NCD2



GET-AL
Jaw coupling,
economy range,
Aluminium



E15
Right angle helical
reducers, from 0.40 to
5.5



J52
Spur gear coaxial
gearbox, from 0.27 to
5.5



CLASS
Stainless steel
indexing handle -



M1
Worm and wheel set,
Hardened steel

Complementary products




PRF1932
Standard aluminium
profile, 19 x 32 mm



PRF4545
Standard stainless
steel profile, 45 x 45
mm



PRF_FIX_UNI
Universal fastener for
aluminium profile,
Universal



PRF4545r90
Standard aluminium
profile, 45 x 45 mm -
R90°