

Profile assembly



- Suitable for loads up to 18000N
- Can be used to securely join all profile types
- Forms very efficient anti-twist joint
- Materials:
M8x50mm CHC screw: electroplated steel
Locking plate: electroplated steel

Uses

- For heavy or vibrating loads

Assembly

- Drill a stepped hole ($\varnothing 9$, $\varnothing 15$) at the required position
- Slide the screw locking plate in the slot
- Pass the end of the screw through the first profile (1), the locking plate and then into the central hole of the second profile (2) which was previously tapped ($M8 \times 25\text{mm}$) and tighten.

**DISCOUNTS**

Qty	1+	50+	100+
Disc.	List	-5%	On request

Part number	Load (N)	For profile	Tightening torque (Nm)	Weight (kg)	Stock*	Price each 1 to 49
PRF-FIX-STD	18000	All types of PRF profile	20	0,03	✓	2,10 €

*Depending on availability - Dimensions in mm

Our other products



ACLEPP

Right angled bracket for aluminium profile, 2 holes




F7-P-AM

Multifunction display, Magnetic band



BLHB30

Right angled gearbox, bored shafts, up to 4.47 Nm



RPPM

RPP type belt per metre, RPP5 Steel cored polyurethane



GET-AL

Jaw coupling, economy range, Aluminium



PR85

Articulated foot Ø83, Ø 83



PRF_GAL

Roller for aluminium profile, Flat roller



BEAS

Star shaped anti-static handle, Star, anti-static



TCC

Rigging screw (hook/hook), Steel



CHT

Asynchronous AC Motor, 0.18 to 0.55kW



GCL

Linear ball slide - Stainless steel balls,



GAL22

Conveyor wheel, Zinc plated steel

Complementary products



PRF1932

Standard aluminium profile, 19 x 32 mm




PRF4545

Standard stainless steel profile, 45 x 45 mm



PRF_FIX_UNI

Universal fastener for aluminium profile, Universal



PRF4545r90

Standard aluminium profile, 45 x 45 mm - R90°