

### Profile assembly




- Suitable for loads up to 18000N
- Can be used to securely join all profile types
- Forms very efficient anti-twist joint
- Materials:  
M8x50mm CHC screw: electroplated steel  
Locking plate: electroplated steel

### Uses

- For heavy or vibrating loads

### Assembly

- Drill a stepped hole ( $\varnothing 9$ ,  $\varnothing 15$ ) at the required position
- Slide the screw locking plate in the slot
- Pass the end of the screw through the first profile (1), the locking plate and then into the central hole of the second profile (2) which was previously tapped ( $M8 \times 25mm$ ) and tighten.



### DISCOUNTS

Qty	1+	50+	100+
Disc.	List	-5%	On request

Part number	Load (N)	For profile	Tightening torque (Nm)	Weight (kg)	Stock*	Price each 1 to 49
PRF-FIX-STD	18000	All types of PRF profile	20	0,03	✓	2,10 €

\*Depending on availability - Dimensions in mm

## Our other products



PRF-GPA  
Guide for aluminium  
profile, Parallel rails



CHB  
Worm and wheel gear  
reducer, up to 22 Nm



BSM\_LOK  
Long-Lok spring  
plunger with internal  
hexagonal socket,  
LONG-LOK - s...



CHINV  
Invisible hinge,  
Invisible - Opening up  
to 90°



NK17  
Drylin®N miniature  
guiding system, Width  
17 mm



DFG  
Flat suction cup,  
nitrile



BAC105  
Storage bin, 8mm



ZDB  
Machined plastic  
bevel gear, 2:1



V3RA\_PTR  
3-spoked handwheel  
with foldable handle,  
Polyamide



ACM\_AZ  
Mounting bracket for  
bonnet fastener, Hook



PLM-20SC  
Cylindrical magnet,  
Cylindrical magnet



PTA80  
Articulated levelling  
foot, pressed base  
Ø80, Ø 80

## Complementary products




PRF1932  
Standard aluminium  
profile, 19 x 32 mm



PRF4545  
Standard stainless  
steel profile, 45 x 45  
mm



PRF\_FIX\_UNI  
Universal fastener for  
aluminium profile,  
Universal



PRF4545r90  
Standard aluminium  
profile, 45 x 45 mm -  
R90°