

Profile assembly




- Suitable for loads up to 18000N
- Can be used to securely join all profile types
- Forms very efficient anti-twist joint
- Materials:
M8x50mm CHC screw: electroplated steel
Locking plate: electroplated steel

Uses

- For heavy or vibrating loads

Assembly

- Drill a stepped hole ($\varnothing 9$, $\varnothing 15$) at the required position
- Slide the screw locking plate in the slot
- Pass the end of the screw through the first profile (1), the locking plate and then into the central hole of the second profile (2) which was previously tapped ($M8 \times 25mm$) and tighten.



DISCOUNTS

Qty	1+	50+	100+
Disc.	List	-5%	On request

Part number	Load (N)	For profile	Tightening torque (Nm)	Weight (kg)	Stock*	Price each 1 to 49
PRF-FIX-STD	18000	All types of PRF profile	20	0,03	✓	2,10 €

*Depending on availability - Dimensions in mm

Our other products



RHTplss
High Temperature
Castor, up to 200kg



BOX-TOR-B
Box set of Nitrile O-
rings in nitrile, 20.38 x
1.78mm to 50.16 x
5.34




WJRM
Drylin® W hybrid
bearing block, Hybrid
bearings



PTA80
Articulated levelling
foot, pressed base
Ø80, Ø 80



CFUURSS
Cam follower stainless
steel, Standard -
stainless steel



TBV
Manual lifting tables,
7kg



BTE
Universal tension arm,
For normal
applications



NSO
Housing for open
linear bearing,
Opened - long



PSG08
Spur gear - precision
range, Case hardened



FF50
Offset spur gear
reducer, from 111 to



RFV50
Stainless steel worm
and wheel gearbox,



PW_PWG25
Worm - precision
range, Steel

Complementary products




PRF1932
Standard aluminium
profile, 19 x 32 mm



PRF4545
Standard stainless
steel profile, 45 x 45
mm



PRF_FIX_UNI
Universal fastener for
aluminium profile,
Universal



PRF4545r90
Standard aluminium
profile, 45 x 45 mm -
R90°