

Profile assembly



- Suitable for loads up to 18000N
- Can be used to securely join all profile types
- Forms very efficient anti-twist joint
- Materials:
M8x50mm CHC screw: electroplated steel
Locking plate: electroplated steel

Uses

- For heavy or vibrating loads

Assembly

- Drill a stepped hole ($\varnothing 9$, $\varnothing 15$) at the required position
- Slide the screw locking plate in the slot
- Pass the end of the screw through the first profile (1), the locking plate and then into the central hole of the second profile (2) which was previously tapped ($M8 \times 25\text{mm}$) and tighten.

**DISCOUNTS**

Qty	1+	50+	100+
Disc.	List	-5%	On request

Part number	Load (N)	For profile	Tightening torque (Nm)	Weight (kg)	Stock*	Price each 1 to 49
PRF-FIX-STD	18000	All types of PRF profile	20	0,03	✓	2,10 €

*Depending on availability - Dimensions in mm

Our other products



BPL
Ball transfer unit light
duty, Light



HDSS
Needle roller double
universal joint -
Stainless steel, Heavy
duty



CHB
Double output shaft,
For CHB gearbox



SLVVlok
Vertical toggle clamp,
Vertical toggle clamp /
vertical foot



IBjss
Ball and socket joint,
Stainless steel



PRF4545_P
Stripp Aluminium
profile with
extendable slot, 45 x
45 mm



NRV
Orthogonal support
clamp, Orthogonal
support clamp



ZAmM
Shaft for linear
guides, Hardened
ground steel



HTD8M-BAR
HTD type tooth bar
stock, HTD8



PP35
Worm and wheel gear
reducer, from 2.20



ZG2
Plastic spur gear,
Machined plastic



SME
Male rod ends,
Stainless steel / PTFE

Complementary products




PRF1932
Standard aluminium
profile, 19 x 32 mm



PRF4545
Standard stainless
steel profile, 45 x 45
mm



PRF_FIX_UNI
Universal fastener for
aluminium profile,
Universal



PRF4545r90
Standard aluminium
profile, 45 x 45 mm -
R90°