

Profile assembly



- Suitable for loads up to 18000N
- Can be used to securely join all profile types
- Forms very efficient anti-twist joint
- Materials:
M8x50mm CHC screw: electroplated steel
Locking plate: electroplated steel

Uses

- For heavy or vibrating loads

Assembly

- Drill a stepped hole ($\varnothing 9$, $\varnothing 15$) at the required position
- Slide the screw locking plate in the slot
- Pass the end of the screw through the first profile (1), the locking plate and then into the central hole of the second profile (2) which was previously tapped ($M8 \times 25\text{mm}$) and tighten.

**DISCOUNTS**

Qty	1+	50+	100+
Disc.	List	-5%	On request

Part number	Load (N)	For profile	Tightening torque (Nm)	Weight (kg)	Stock*	Price each 1 to 49
PRF-FIX-STD	18000	All types of PRF profile	20	0,03	✓	2,10 €

*Depending on availability - Dimensions in mm

Our other products



V3RA_PTR

3-spoked handwheel
with foldable handle,
Polyamide



CHAFR-MINI

Miniature friction
hinge, Friction



PW_PWG1

Wheel - precision
range, Bronze



EPRC

High helix leadscrew,
Cylindrical nut - up to
40mm per rotation



IBJss

Ball and socket joint,
Stainless steel



LINK64

Synchronous AC
Motor and- gearbox ,
from 1.3 to 6Nm




PDD

Actuating plunger,
Non-rotating detector
shaft



SVG

Adjustable latch
clamp with strike
plate, Stroke from
82mm to 92mm



IN1

Internal gear,
Machined plastic



NIN

Self-locking nut, Steel



BABS303

303 Stainless steel
compact ball pin,



ATZY

Diabolo shaped elasto
mount, Steel

Complementary products



PRF1932

Standard aluminium
profile, 19 x 32 mm




PRF4545

Standard stainless
steel profile, 45 x 45
mm



PRF_FIX_UNI

Universal fastener for
aluminium profile,
Universal



PRF4545r90

Standard aluminium
profile, 45 x 45 mm -
R90°