

Articulated foot with sheet metal base Ø100

PAMF100

Max load: 15,000N
Rubber sole in EPDM, blue



- **Articulated adjustable levelling feet**
- Axial articulation +/- 10°
- With non-slip sole in EPDM Blue
- Stainless steel in shiny finish
- Materials:
 - Base: shiny 304 stainless steel sheet
 - Thread: 304 stainless steel, supplied without nut
 - Sole: EPDM blue

Options

- Other thread dimensions on request
- 316 grade Stainless steel on request

Advantages

- Hygienic special pad for easy cleaning.
- Food processing, Pharmaceutical and Chemical Environment



DISCOUNTS

Qty	1+	6+	10+	15+	20+
Disc. Price	-5%	-10%	-10%	-15%	On request


References	Threading		B	A	A/F	G	H	Static load(N)	Price per unit 1 to 5
	ØD	ØF							
PAMF100-16-100/EB	100	M16	100	39.5	13	30	139.5	15000	53,37€
PAMF100-16-150/EB	100	M16	150	39.5	13	30	189.5	15000	54,99€
PAMF100-16-200/EB	100	M16	200	39.5	13	30	239.5	15000	58,69€
PAMF100-20-100/EB	100	M20	100	43.0	17	30	143.0	15000	56,55€
PAMF100-20-150/EB	100	M20	150	43.0	17	30	193.0	15000	59,76€
PAMF100-20-200/EB	100	M20	200	43.0	17	30	243.0	15000	63,46€

* Depending on availability - Dimensions in mm

Our other products



Spur gear coaxial gearbox, from 0.90 to 2.80 Nm - Inline



Standard aluminium profile, 45 x 45 mm - R90°



Ball transfer unit push fit, Light



Angular connector, Universal angular connector



Parallel axis helical gear, Machined plastic (delrin)




Cylindrical steel nut, Steel - 1 thread



Idle sprocket for slat top chain, Range 881



Cylindrical ballscrew nut, Cylindrical nut - Multiple starts




1A motorised linear actuator, 1 ampere



Connecting plate for T type timing belts, T10



Drylin® W rail, Rail



Stainless steel manual rigging screw, Stainless steel - manual

Complementary products



Articulated foot with sheet metal base
Ø50, Articulated foot



Articulated foot with sheet metal base
Ø80, Articulated foot



Articulated foot with sheet metal base
Ø100, Articulated foot



Articulated foot with sheet metal base
Ø80, Articulated foot