

Profile assembly




- Suitable for loads up to 18000N
- Can be used to securely join all profile types
- Forms very efficient anti-twist joint
- Materials:
M8x50mm CHC screw: electroplated steel
Locking plate: electroplated steel

Uses

- For heavy or vibrating loads

Assembly

- Drill a stepped hole ($\varnothing 9$, $\varnothing 15$) at the required position
- Slide the screw locking plate in the slot
- Pass the end of the screw through the first profile (1), the locking plate and then into the central hole of the second profile (2) which was previously tapped ($M8 \times 25mm$) and tighten.



DISCOUNTS

Qty	1+	50+	100+
Disc.	List	-5%	On request

Part number	Load (N)	For profile	Tightening torque (Nm)	Weight (kg)	Stock*	Price each 1 to 49
PRF-FIX-STD	18000	All types of PRF profile	20	0,03	✓	2,10 €

*Depending on availability - Dimensions in mm

Our other products



TCC
Rigging screw
(hook/hook), Steel




AT5M AT10M
AT type timing belt
per metre, AT5 Steel
cored polyurethane



LRRss
Latch, Spring loaded
latch - stainless steel



PT820
Drive sprocket for slat
top chain, Ranges 820
and 815



ACLBT5
Closing system for
aluminium profile, 90°
bracket for spherical
end...



KH
Linear bearing, Light



BTCW
Cap for square tube to
be welded, To be
welded



RCX-6
Spherical tilt washer -
DIN6319, concave



LWH
High rigidity linear
slide, Rail - from 9320



UTKswcr
Utilittrak® 3 wheels
carriage, Steel roller



AC
Strike for toggle latch,
15mm



WJUM20
Drylin® W bearing
block, Slide

Complementary products




PRF1932
Standard aluminium
profile, 19 x 32 mm



PRF4545
Standard stainless
steel profile, 45 x 45
mm



PRF_FIX_UNI
Universal fastener for
aluminium profile,
Universal



PRF4545r90
Standard aluminium
profile, 45 x 45 mm -
R90°