

Pull handle

PCA



Thermoplastic

Gripping handle for both pushing and pulling

- Rear mounting
- Working T° -30°C to +130°C
- Materials:
 - Thermoplastic PA6 glass fiber reinforced
 - Brass inserts with tapped blind hole

Advantages

- Very strong
- 110mm and 120mm centres correspond to German standards
- No product retention



DISCOUNTS

Qty	1+	6+	20+	50+	100+	250+
Disc.	List	-5%	-10%	-15%	-20%	On request

Part number	B	A	E	F	C	H	ØD	Weight (g)	Stock*	Price each 1 à 5
PCA93-M5	93,5±0,5	111	23	36	29	9	M5	41	-	5,31 €
PCA93-M6	93,5±0,5	111	23	36	29	9	M6	42	-	5,31 €
PCA105-M5	105±0,5	121	26	37	29	9	M5	46	-	5,67 €
PCA105-M6	105±0,5	121	26	37	29	9	M6	48	-	5,67 €
PCA110-M5	110±0,5	133	26	40	32	9	M5	58	-	6,18 €
PCA110-M6	110±0,5	133	26	40	32	9	M6	60	-	6,18 €
PCA117-M5	117±1	133	26	40	32	9	M5	57	-	6,39 €
PCA117-M6	117±1	133	26	40	32	9	M6	59	-	6,39 €
PCA117-M8	117±1	133	26	40	32	9	M8	61	-	6,39 €
PCA120-M8	120±1	137	26	40	32,5	9	M8	58	-	6,48 €
PCA132-M8	132±1	150	26	45	37	9	M8	68	-	7,38 €
PCA150-M8	150±1	169	27	45	37	9	M8	76	-	8,25 €
PCA179-M8	179±1	200	28	51	42	9	M8	101	-	9,42 €
PCA179-M10	179±1	200	28	51	42	13	M10	101	-	9,45 €

*Depending on availability - Dimensions in mm

Our other products



CDPC
Flanged drill bushing,
Steel



PFM
Fixed levelling foot,
Flanged plate



SDCcs
Positioning sleeve for
indexing pin, For pin
Ø4 to Ø12



DOMI30
Connecting kits, XZ
linking kit



H02
Single needle roller
universal joint, Heavy
duty



BH02
Single housed bearing
assembly, Bearing
secured with circlips



IBJss
Ball and socket joint,
Stainless steel




CLR
Straight clevis,
Straight clevis for use
with a male clevis



MSP3815
Masterplate®
glueable insert
rectangular,



HRV
V- rail guidance
Simple Select®
system, Rail with



H0
Crossed helical gear
crossed axis at 90°,
Machined plastic



AT5P_AT10P
Connecting plate for
AT type timing belts,
AT5


Complementary products




PO
Pull handle - Multi-
sector, Smooth hole



PO
Pull handle - Multi-
sector, Tapped
recessed insert



PO
Pull handle - Multi-
sector, Smooth hole



PO
Pull handle - Multi-
sector, Smooth hole