

Solid stainless steel articulated foot Ø30 Sta


PRS30

Max load up to 10,000N

- **Levelling foot**
- Oscillation +/- 15° with respect to the axis
- With non-slip sole
- **Materials:**
 - Base: AISI 304 stainless steel
 - Rod: stainless steel AISI 304 (nut not supplied)
 - Sole: rubber NBR hardness 70° Shore, non-slip

Advantages

- The rod with its ball-and-socket arrangement allows self-alignment with the ground
- The sole is designed to give flexibility and grip



DISCOUNTS

Qty	1+	6+	10+	15+
Disc.	Net	-5%	-10%	On request

Part N°	ØM	A	B	ØD	A/F	G	H	H1	Static load (N)	Price each 1 to 5
PRS30-6-25	M6	23,5	25	30	12	13	48,5	49	5000	22,04 €
PRS30-6-50	M6	23,5	50	30	12	13	73,5	74	5000	23,47 €
PRS30-6-75	M6	23,5	75	30	12	13	88,5	89	5000	24,94 €
PRS30-8-25	M8	23,5	25	30	12	13	48,5	49	8000	22,04 €
PRS30-8-50	M8	23,5	50	30	12	13	73,5	74	8000	23,47 €
PRS30-8-75	M8	23,5	75	30	12	13	88,5	89	8000	24,94 €
PRS30-8-100	M8	23,5	100	30	12	13	123,5	124	8000	28,62 €
PRS30-10-25	M10	23,5	25	30	12	13	48,5	49	10000	22,04 €
PRS30-10-50	M10	23,5	50	30	12	13	73,5	74	10000	23,47 €
PRS30-10-75	M10	23,5	75	30	12	13	88,5	89	10000	24,94 €
PRS30-10-100	M10	23,5	100	30	12	13	123,5	124	10000	28,62 €
PRS30-10-125	M10	23,5	125	30	12	13	148,5	149	10000	26,92 €
PRS30-12-25	M12	23,5	25	30	12	13	48,5	49	10000	22,04 €
PRS30-12-50	M12	23,5	50	30	12	13	73,5	74	10000	23,47 €
PRS30-12-75	M12	23,5	75	30	12	13	88,5	89	10000	24,94 €
PRS30-12-100	M12	23,5	100	30	12	13	123,5	124	10000	26,41 €
PRS30-12-125	M12	23,5	125	30	12	13	148,5	149	10000	27,89 €
PRS30-12-150	M12	23,5	150	30	12	13	173,5	174	10000	29,36 €

* Subject to available stocks- All dimensions in mm


Our other products



MHPGR
Arm with folding rotating handle,



EKGS
Backlash free coupling Gerwah®, from 0.5 to 35Nm




AC
Strike for toggle latch, 20mm



SH1
Parallel axis helical gear, Machined plastic (delrin)



SVR20
Screwjack with travelling nut, with moving nut



PRF-SCREEN-1
Screen support, Basic support




CHNrb
Warning chain with red and white links, Steel



LSAG
Precision linear rotary ball spline, Rail - from 514 N to 15386 N



PCS25ECO
Chain sprocket - steel, 6.35mm



P40
Worm and wheel gear reducer, up to 18 Nm



LPCM
Lever with cylindrical handle, Black Duroplast, steel lever



SLVV|ok
Vertical toggle clamp, Vertical toggle clamp / vertical foot

Complementary products



PR550
Stainless steel articulated foot Ø50, Ø 50



PAM_SS
Stainless steel articulated levelling foot, Ø 30 & 40