

Clamp lever with threaded insert



With thread insert

PCLAM

PCLAMSS

- Control lever with threaded insert

- Materials:

Insert: steel (class 5.8) or stainless steel (303)

Handle: glass fibre reinforced polyamide plastic

Mechanism: splined diecast zinc

- Finish: Blackened steel

- Color : black

Uses


- The lever is normally in a locked position

- Raise the handle to release the lever and turn to required position

- When handle is released, lever will automatically lock in new position

Info.

- H4 = clearance height required for handle



Part number	Thread	X	T	ØD	ØD1	H	H1	H2
PCLA01M4	M4	9	10,0	13,0	13,0	24,5	4,0	15,0
PCLA01M5	M5	9	10,0	13,0	13,0	24,5	4,0	15,0
PCLA01M6	M6	9	10,0	13,0	13,0	24,5	4,0	15,0
PCLA02M6	M6	12	13,5	18,0	18,0	28,5	6,5	17,5
PCLA02M8	M8	12	13,5	18,0	18,0	28,5	6,5	17,5
PCLA03M8	M8	14	16,0	21,5	21,5	37,0	10,0	24,0
PCLA03M10	M10	14	16,0	21,5	21,5	37,0	10,0	24,0
PCLA04M10	M10	17	19,0	25,5	25,5	43,0	10,0	26,0
PCLA04M12	M12	17	19,0	25,5	25,5	43,0	10,0	26,0
PCLA05M12	M12	23	23,0	30,0	30,0	49,0	12,0	33,0
PCLA05M16	M16	23	23,0	30,0	30,0	49,0	12,0	33,0

Stock*								
Part number	Steel	Stainless	H3	H4	A	A1	B	Steel
								StS
PCLA01M4	-		30,0	33,5	40	47,0	7,5	✓
PCLA01M5	PCLA01M5SS		30,0	33,5	40	47,0	7,5	✓
PCLA01M6	PCLA01M6SS		30,0	33,5	40	47,0	7,5	✓
PCLA02M6	PCLA02M6SS		41,5	45,5	65	75,0	9,5	✓
PCLA02M8	PCLA02M8SS		41,5	45,5	65	75,0	9,5	✓
PCLA03M8	PCLA03M8SS		53,5	58,0	80	91,5	11,0	✓
PCLA03M10	PCLA03M10SS		53,5	58,0	80	91,5	11,0	✓
PCLA04M10	PCLA04M10SS		61,0	66,0	95	109,0	13,0	✓
PCLA04M12	PCLA04M12SS		61,0	66,0	95	109,0	13,0	✓
PCLA05M12	PCLA05M12SS		72,0	77,0	110	126,0	15,5	✓
PCLA05M16	PCLA05M16SS		72,0	77,0	110	126,0	15,5	✓

*Depending on availability - Dimensions in mm

Our other products



PDM_PDV

Detectable plastic palm grip, by metal detectors



S_2RS

Deep groove ball bearing, Stainless steel



MFBSC

Stainless steel flexible bellows coupling, Stainless steel - with cl...



GP75

Spring loaded toggle latch, Standard (GP75)



HW_HT

Half-rail guide, Rail



PF45

Worm and wheel gear reducer, up to 40 Nm



TFR

Rigid manual tensioner, Fixed



SH0

Parallel axis helical gear, Machined plastic (delrin)



LVT

Miniature motorised actuator 1A, 1 amper



PTAF100-PAMF100

Articulated fixable foot with pressed base Ø100, Ø 100



G-ECO

Eco range Spur gear, Steel C45



HRV

V- rail guidance Simple Select® system, Rail with carriage

Complementary products



CLB_M

Die cast zinc clamping lever - female, Zamak



CLASS

Stainless steel indexing handle - female, Stainless steel



CLASS

Stainless steel indexing handle - male, Stainless steel