Stainless steel articulated foot Ø50 Stock


PRS50 — Maximum load 15.000N

- ***Solid levelling support***
- *With non-slip base*
- *Materials:*
  Base: stainless steel AISI 304
  Threaded rod: stainless steel AISI 304 (nut not supplied)
  Sole: NBR rubber (Shore hardness 70)



Advantages

- *Articulated rod allows auto-alignment with the ground*
- *Sole material ensures flexibility and grip*




DISCOUNTS

Qty	1+	6+	10+	15+
Disc.	List	-5%	-10%	On request

Part number	ØM	A	B	ØD	A/F	G	H	H1	Max. load (N)	Stock*	Price each 1 to 5
PRS50-10-50	M10	28	50	50	14	16	78	81	15000	✔	37,51 €
PRS50-10-75	M10	28	75	50	14	16	103	106	15000	✔	39,98 €
PRS50-10-100	M10	28	100	50	14	16	128	131	15000	✔	42,31 €
PRS50-10-125	M10	28	125	50	14	16	153	156	15000	✔	44,61 €
PRS50-12-50	M12	28	50	50	14	16	78	81	15000	✔	37,51 €
PRS50-12-75	M12	28	75	50	14	16	103	106	15000	✔	39,98 €
PRS50-12-100	M12	28	100	50	14	16	128	131	15000	✔	42,31 €
PRS50-12-125	M12	28	125	50	14	16	153	156	15000	✔	44,61 €
PRS50-14-50	M14	28	50	50	14	16	78	81	15000	✔	37,51 €
PRS50-14-75	M14	28	75	50	14	16	103	106	15000	✔	39,98 €
PRS50-14-100	M14	28	100	50	14	16	128	131	15000	✔	42,31 €
PRS50-14-125	M14	28	125	50	14	16	153	156	15000	✔	44,61 €

**Depending on availability - Dimensions in mm*

Our other products



Flanged leadscrew nut, Flanged nut - Multiple starts



Sealing washer Hygienic Usit®, Stainless steel - Black EPDM



Cylindrical spacer, Thermoplastic



Worm and wheel gear reducer, up to 3,75 Nm



Closed linear precision bearing, Economy range



Asynchronous AC motorgearboxes 0.37 to 1.5kW, 0.37 to 1.5kW



Eye bolt, Steel



Spur gear with clamp, Stainless steel 303



Wheel - precision range, Bronze



Mushroom headed button, M3 to M8



Domino 30 adjustable slide, Slide DOMILINE 30 with counter and



Worm and wheel gear reducer, up to 164 Nm

Complementary products



Stainless steel articulated foot Ø30, Ø 30



Stainless steel articulated foot Ø80, Ø 80



Stainless steel articulated foot Ø100, Ø 100