



# Clamp lever

With male thread

PCLAT  
PCLATss

- Clamp lever with male thread and reduced tip according to DIN 78

- Materials:

Insert: steel (class 5.8) or stainless steel (303)

Handle: glass fibre reinforced polyamide plastic

Mechanism: splined diecast zinc

- Finish: Blackened steel, fine grained surface

- Matte surface with fine grains

- Colour: black

- Working temp.: -50°C to +130°C

## Uses

- The lever is normally in a locked position
- Raise the handle to release the lever and turn to required position
- When handle is released, lever will automatically lock in new position

## Info.

- H4 = clearance height required for handle



## DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-10%	On request

Part number		Threaded bolt X	L						
Steel	Stainless		H1	Steel	StS	ØD	ØD1	H	
PCLA01T5	PCLA01T5SS	M5	4,0	50	25	10,0	13,0	24,5	
PCLA01T6	PCLA01T6SS	M6	4,0	50	50	10,0	13,0	24,5	
PCLA02T8	PCLA02T8SS	M8	6,5	60	60	13,5	18,0	28,5	
PCLA02T10	PCLA02T10SS	M10	6,5	60	60	13,5	18,0	28,5	
PCLA03T10	PCLA03T10SS	M10	10,0	60	60	16,0	21,5	37,0	
PCLA04T10	-	M10	10,0	90	-	19,0	25,5	43,0	
PCLA04T12	PCLA04T12SS	M12	10,0	90	60	19,0	25,5	43,0	
PCLA05T12	-	M12	12,0	90	-	23,0	30,0	49,0	
PCLA05T16	PCLA05T16SS	M16	12,0	90	60	23,0	30,0	49,0	


Part number									Stock*	Price each 1 to 5	
Steel	Stainless	A	H2	H3	H4	A1	B		Steel	StS	
PCLA01T5	PCLA01T5SS	40	15,0	30,0	33,5	47,0	7,5	✓	✓	✓	9,83 € 13,52 €
PCLA01T6	PCLA01T6SS	40	15,0	30,0	33,5	47,0	7,5	✓	✓	✓	9,83 € 14,53 €
PCLA02T8	PCLA02T8SS	65	17,5	41,5	45,5	75,0	9,5	✓	✓	✓	11,46 € 17,36 €
PCLA02T10	PCLA02T10SS	65	17,5	41,5	45,5	75,0	9,5	✓	✓	✓	11,46 € 17,36 €
PCLA03T10	PCLA03T10SS	80	24,0	53,5	58,0	91,5	11,0	✓	✓	✓	14,14 € 21,57 €
PCLA04T10	-	95	26,0	61,0	66,0	109,0	13,0	✓	-	✓	18,72 € -
PCLA04T12	PCLA04T12SS	95	26,0	61,0	66,0	109,0	13,0	✓	-	✓	18,72 € 31,50 €
PCLA05T12	-	110	33,0	72,0	77,0	126,0	15,5	-	-	✓	23,18 € -
PCLA05T16	PCLA05T16SS	110	33,0	72,0	77,0	126,0	15,5	-	-	✓	23,18 € 37,27 €

\*Depending on availability - Dimensions in mm

## Our other products



PRF\_GAL  
Roller for aluminium profile, Fixing kit for roller concentric



CHB  
Worm and wheel gear reducer, up to 41 Nm



PPG  
Indexing plunger with flange, With horizontal mounting flange



M0  
Worm and wheel set, Unhardened steel



BWU  
Compact precision slide, from 1510 N to 10500 N



NIN  
Self-locking nut, Steel



SSG2\_304L  
Stainless steel spur gear, Stainless steel 304L



BOXKU  
Boxed set of half round (Woodruff) keys NFE22179, Boxed set of half ...



LRR  
Spring loaded latch, Spring loaded latch



PFM  
Fixed levelling foot, Flanged plate



PRF-SRA-78  
Lock for aluminium profile, Quick fitting, self locking door lock



GLT2-17  
Telescopic drawer runners for groove mounting, Partial extension

## Complementary products



CLB\_T  
Die cast zinc clamping lever - male, Zamak



CLASS  
Stainless steel indexing handle - male, Stainless steel



CLB\_T  
Die cast zinc clamping lever - male, Zamak



CLB\_M  
Die cast zinc clamping lever - female, Zamak