


- Levelling foot with solid base
- Non slip base
- Materials:
  - Base: stainless steel AISI 304
  - Threaded rod: stainless steel AISI 304 (nut not supplied)
  - Sole: NBR rubber (Shore hardness 70)

### Advantages

- Articulated rod allows auto-alignment with the ground
- Sole material ensures flexibility and grip



stainless steel



### DISCOUNTS

Qty	1+	6+	10+	15+
Disc.	List	-5%	-10%	On request

Part number	ØM	A	B	ØD	A/F	G	H	H1	Max. load (N)	Stock*	Price each 1 to 5
										✓	
PRS80-16-50	M16	36	50	80	13	19,5	86	89	30000	✓	79,02 €
PRS80-16-75	M16	36	75	80	13	19,5	111	114	30000	-	79,87 €
PRS80-16-100	M16	36	100	80	13	19,5	136	139	30000	✓	80,82 €
PRS80-16-125	M16	36	125	80	13	19,5	159	164	30000	-	81,65 €
PRS80-16-150	M16	36	150	80	13	19,5	186	189	30000	-	82,61 €
PRS80-16-175	M16	36	175	80	13	19,5	211	214	30000	✓	83,46 €
PRS80-16-200	M16	36	200	80	13	19,5	236	239	30000	✓	84,42 €
PRS80-20-75	M20	36	75	80	13	19,5	111	114	30000	-	81,27 €
PRS80-20-100	M20	36	100	80	13	19,5	136	139	30000	-	82,16 €
PRS80-20-125	M20	36	125	80	13	19,5	161	164	30000	-	83,04 €
PRS80-20-150	M20	36	150	80	13	19,5	186	189	30000	-	83,95 €
PRS80-20-175	M20	36	175	80	13	19,5	211	214	30000	✓	84,83 €
PRS80-20-200	M20	36	200	80	13	19,5	236	239	30000	-	85,76 €
PRS80-20-225	M20	36	225	80	13	19,5	261	264	30000	-	86,65 €

\*Depending on availability - Dimensions in mm

## Our other products



BCM\_MPBT

Modular cylindrical brush, PBT polyester bristles




MCL

Cylindrical threaded sleeve, Cylindrical - stainless steel



CHM30

Worm and wheel gear reducer, up to 28 Nm



BAG-MISS

Split shaft collar with clamp lever, Stainless steel



NT61

Spur gear coaxial gearbox, from 5 to 14 Nm - In-line




PR881

Idler sprocket for slat top chain, Range 881



PTKFss

Fixable foot for the food industry, Stainless steel - 3-A standard



RDERSS

Stainless steel manual rigging screw, Stainless steel - manual



PTA40

Articulated foot with solid base foot Ø 40,



RBN

Wheel, Rubber tyre - Polypropylene rim



HLUMss

Revolving handle for handwheel, Stainless



DFG

Flat suction cup, nitrile

## Complementary products



PR85

Articulated foot Ø83, Ø 83