



Clamp lever

With male thread

PCLAT PCLATss

- **Clamp lever with male thread and reduced tip according to DIN 78**

- **Materials:**

Insert: steel (class 5.8) or stainless steel (303)

Handle: glass fibre reinforced polyamide plastic

Mechanism: splined diecast zinc



- **Finish:** Blackened steel, fine grained surface

- **Matte surface with fine grains**

- **Colour:** black

- **Working temp.:** -50°C to +130°C

With male thread



Uses

- The lever is normally in a locked position

- Raise the handle to release the lever and turn to required position

- When handle is released, lever will automatically lock in new position

Info.

- H4 = clearance height required for handle

DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-10%	On request

Part number		Threaded bolt X	H1	L			ØD	ØD1	H
Steel	Stainless			Steel	StS				
PCLA01T5	PCLA01T5SS	M5	4,0	50	25	10,0	13,0	24,5	
PCLA01T6	PCLA01T6SS	M6	4,0	50	50	10,0	13,0	24,5	
PCLA02T8	PCLA02T8SS	M8	6,5	60	60	13,5	18,0	28,5	
PCLA02T10	PCLA02T10SS	M10	6,5	60	60	13,5	18,0	28,5	
PCLA03T10	PCLA03T10SS	M10	10,0	60	60	16,0	21,5	37,0	
PCLA04T10	-	M10	10,0	90	-	19,0	25,5	43,0	
PCLA04T12	PCLA04T12SS	M12	10,0	90	60	19,0	25,5	43,0	
PCLA05T12	-	M12	12,0	90	-	23,0	30,0	49,0	
PCLA05T16	PCLA05T16SS	M16	12,0	90	60	23,0	30,0	49,0	

Part number		Stock*							Price each 1 to 5		
Steel	Stainless	A	H2	H3	H4	A1	B	Steel	StS	Steel	Stainless
PCLA01T5	PCLA01T5SS	40	15,0	30,0	33,5	47,0	7,5	✓	✓	9,83 €	13,52 €
PCLA01T6	PCLA01T6SS	40	15,0	30,0	33,5	47,0	7,5	✓	✓	9,83 €	14,53 €
PCLA02T8	PCLA02T8SS	65	17,5	41,5	45,5	75,0	9,5	✓	✓	11,46 €	17,36 €
PCLA02T10	PCLA02T10SS	65	17,5	41,5	45,5	75,0	9,5	✓	✓	11,46 €	17,36 €
PCLA03T10	PCLA03T10SS	80	24,0	53,5	58,0	91,5	11,0	✓	✓	14,14 €	21,57 €
PCLA04T10	-	95	26,0	61,0	66,0	109,0	13,0	✓	-	18,72 €	-
PCLA04T12	PCLA04T12SS	95	26,0	61,0	66,0	109,0	13,0	✓	✓	18,72 €	31,50 €
PCLA05T12	-	110	33,0	72,0	77,0	126,0	15,5	-	-	23,18 €	-
PCLA05T16	PCLA05T16SS	110	33,0	72,0	77,0	126,0	15,5	-	-	23,18 €	37,27 €

*Depending on availability - Dimensions in mm


Our other products



M1
Worm and wheel set,
Machined plastic
(delrin)



RAM30
Manual bevel
gearbox, Bevel



RPPM
RPP type belt per
metre, RPP8 Steel
cored polyurethane



CHT
Asynchronous AC
motor 0.12 to 0.22kW,
0.12 to 0.22kW



BAGSS
Stainless steel
Clamping collar,
Stainless steel



BEAS
Knob star grip
antistatic, Star, anti-
static



SLHVlok
Horizontal toggle
clamp, Horizontal
toggle clamp / vertical
foot



AT5courroie
AT type timing belt,
AT5 Steel cored
polyurethane



GAL_20
Conveyor roller for
Ø20mm spindle, Self-
lubricating polyamide



CNA-CNG
Right angled
mounting plate, Right
angled mounting



NCT
Square tube
connector, Fixed
angle



E60B
Right angle helical
reducers, from 4.50 to
24 Nm

Complementary products



CLB_T
Die cast zinc clamping
lever - male, Zamak



CLASS
Stainless steel
indexing handle -
male, Stainless steel



PCLA_M
Technopolymer
clamping lever -
female, Plastic



CLB_M
Die cast zinc clamping
lever - female, Zamak