

With male thread

PCLAT PCLATSS

- Clamp lever with male thread and reduced tip according to DIN 78

- Materials:

Insert: steel (class 5.8) or stainless steel (303)Handle: glass fibre reinforced

polyamide plastic Mechanism: splined diecast zinc - Finish: Blackened steel, fine

- grained surface - Matte surface with fine grains
- Colour: black
- Working temp.: -50°C to +130°C

- The lever is normally in a locked position - Raise the handle to release the lever and turn to required position
- When handle is released, lever will automatically lock in new position

Info.

- H4 = clearance height required for handle



Part number		Threaded						
Steel	Stainless	bolt X	H1	Steel	StS	ØD	ØD1	н
PCLA01T5	PCLA01T5SS	M5	4,0	50	25	10,0	13,0	24,5
PCLA01T6	PCLA01T6SS	M6	4,0	50	50	10,0	13,0	24,5
PCLA02T8	PCLA02T8SS	M8	6,5	60	60	13,5	18,0	28,5
PCLA02T10	PCLA02T10SS	M10	6,5	60	60	13,5	18,0	28,5
PCLA03T10	PCLA03T10SS	M10	10,0	60	60	16,0	21,5	37,0
PCLA04T10	-	M10	10,0	90	-	19,0	25,5	43,0
PCLA04T12	PCLA04T12SS	M12	10,0	90	60	19,0	25,5	43,0
PCLA05T12	-	M12	12,0	90	-	23,0	30,0	49,0
PCLA05T16	PCLA05T16SS	M16	12,0	90	60	23,0	30,0	49,0

Part nu						Stock*		Price each 1 to 5			
Steel	Stainless	Α	H2	H3	H4	A1	В	Steel	StS	Steel	Stainless
PCLA01T5	PCLA01T5SS	40	15,0	30,0	33,5	47,0	7,5	~	~	9,83 €	13,52 €
PCLA01T6	PCLA01T6SS	40	15,0	30,0	33,5	47,0	7,5	~	~	9,83 €	14,53 €
PCLA02T8	PCLA02T8SS	65	17,5	41,5	45,5	75,0	9,5	~	~	11,46 €	17,36 €
PCLA02T10	PCLA02T10SS	65	17,5	41,5	45,5	75,0	9,5	V	~	11,46 €	17,36 €
PCLA03T10	PCLA03T10SS	80	24,0	53,5	58,0	91,5	11,0	V	V	14,14 €	21,57 €
PCLA04T10	-	95	26,0	61,0	66,0	109,0	13,0	~	-	18,72 €	-
PCLA04T12	PCLA04T12SS	95	26,0	61,0	66,0	109,0	13,0	~	~	18,72 €	31,50 €
PCLA05T12	-	110	33,0	72,0	77,0	126,0	15,5	-	-	23,18 €	-
PCLA05T16	PCLA05T16SS	110	33,0	72,0	77,0	126,0	15,5	-	_	23,18 €	37,27 €

*Depending on availability - Dimensions in mm





Our other products



Male eye bolt conforms to DIN580, Steel



Wing screw, hand tightened DIN316, Brass DIN 316



Slim slat top chain acetal, Narrow straight range 820



Antistatic brush, Standard



Steel bevel gear, 2:1



Spur gear - precision range, Stainless steel 316



HEAVY DUTY spur gear, Steel 35NCD6



AT type timing belt, AT10 Steel cored polyurethane



Long-Lok slotted spring plunger with ball tip, LONG-LOK -



Roller for aluminium profile, Fixing kit for roller eccentric



Brush strip per metre, Black striated polypropylene (PP)



Spur gear - precision range, Pre-hardened Steel 35NCD6

Complementary products



Die cast zinc clamping lever - male, Zamak



Stainless steel indexing handle male, Stainless steel



Die cast zinc clamping lever - male, Zamak



Die cast zinc clamping lever - female, Zamak