


# Flat magnet




## PLA

## NdFeB


- **Shielded system**
- NdFeB magnets offer 10-20% more attraction force than SmCo magnets
- Max working temp : +80°C
- **Material, finish**  
Galvanised steel body,  
Magnetic core NeFeB




**INCREASED STOCK**



Type A



Type B



Type C

### DISCOUNTS

Qty	1+	6+	20+	40+	60+
Disc.	List	-15%	-20%	-30%	On request

Part number	Forme	ØD	ØD1	ØD2	ØD3	L	L1	Attraction force		Price each 1 to 5
								(N)	(g)	
PLA6-4/A	A	6 <sup>+0,15</sup>	-	-	-	-	4,5	5	1,0	✓ 3,24 €
PLA8-4/A	A	8 <sup>+0,15</sup>	-	-	-	-	4,5	13	1,5	✓ 3,36 €
PLA10-4/A	A	10 <sup>+0,15</sup>	-	-	-	-	4,5	25	2,5	✓ 3,92 €
PLA13-4/A	A	13 <sup>+0,15</sup>	-	-	-	-	4,5	60	4,5	✓ 4,05 €
PLA16-4/A	A	16 <sup>+0,15</sup>	-	-	-	-	4,5	95	6,5	✓ 4,85 €
PLA20-6/A	A	20 <sup>+0,15</sup>	-	-	-	-	6,0	140	15,0	✓ 7,30 €
PLA25-7/A	A	25 <sup>+0,15</sup>	-	-	-	-	7,0	200	22,0	✓ 10,95 €
PLA32-7/A	A	32 <sup>+0,20</sup>	-	-	-	-	7,0	350	40,0	✓ 17,17 €
PLA6-4/B	B	6 <sup>+0,15</sup>	6	M3	-	11,5	4,5	5	1,5	- 4,05 €
PLA8-4/B	B	8 <sup>+0,15</sup>	6	M3	-	11,5	4,5	13	2,0	- 4,20 €
PLA10-4/B	B	10 <sup>+0,15</sup>	6	M3	-	11,5	4,5	25	3,0	✓ 4,81 €
PLA13-4/B	B	13 <sup>+0,15</sup>	6	M3	-	11,5	4,5	60	5,0	✓ 5,02 €
PLA16-4/B	B	16 <sup>+0,15</sup>	6	M4	-	11,5	4,5	95	7,5	✓ 5,87 €
PLA20-6/B	B	20 <sup>+0,15</sup>	8	M4	-	13,0	6,0	140	16,0	- 9,98 €
PLA25-7/B	B	25 <sup>+0,15</sup>	8	M4	-	14,0	7,0	200	25,0	- 14,82 €
PLA32-7/B	B	32 <sup>+0,20</sup>	10	M5	-	15,5	7,0	350	48,0	✓ 20,02 €
PLA10-4/C	C	10 <sup>+0,15</sup>	-	-	M3	11,5	4,5	25	3,0	✓ 4,58 €
PLA13-4/C	C	13 <sup>+0,15</sup>	-	-	M5	12,5	4,5	60	5,0	✓ 5,02 €
PLA16-4/C	C	16 <sup>+0,15</sup>	-	-	M6	12,5	4,5	95	8,0	✓ 5,91 €
PLA20-6/C	C	20 <sup>+0,15</sup>	-	-	M6	16,0	6,0	140	16,0	✓ 10,01 €
PLA25-7/C	C	25 <sup>+0,15</sup>	-	-	M6	17,0	7,0	200	25,0	✓ 14,82 €
PLA32-7/C	C	32 <sup>+0,20</sup>	-	-	M6	17,0	7,0	350	48,0	✓ 20,38 €

Dimensions in mm

## Our other products




Masterplate® glueable insert Ø23, Cylindrical Ø23 with threaded s...



Brush strip per meter PA6 fibres Ø0.2 to Ø0.3, Black polyamide 6 -...



Accessories, Plate



Plastic deep groove ball bearing, Plastic - glass balls material



Self-centering locking Assembly, Medium/low torque




Spiral bevel gear, 1:1



Threaded stud - DIN976A, Stainless steel



3 lobed handle, Polyamide - Steel



RPP heavy duty timing belt, RPP8



Crossed helical gear crossed axis at 90°,



Jaw coupling, economy range,



Spring hinge, screwed

## Complementary products



Flat magnet, Flat magnet



Flat magnet, Flat magnet with threaded hole