


- For driving CAP820 and CAP815 plate chains
- With bore and keyway
- Materials:
 - Reinforced polyamide
 - Stainless steel screws
- Operating temp.: -10°C to +120°C
- For dimensions and bore tolerances, please refer to technical pages


Advantage

- Two part design facilitates easy assembly

Easy assembly



Two part design



DISCOUNTS

Qty	1+	5+	10+
Disc.	List	-5%	On request

Part number	No. of teeth	ØDE	ØDP	Bore ØA	Weight (kg)	Price each 1 to 4
PT820-21-25	21	129	129,26	25	0,4	30,67 €
PT820-21-30	21	129	129,26	30	0,4	30,67 €
PT820-21-35	21	129	129,26	35	0,4	30,67 €
PT820-21-40	21	129	129,26	40	0,4	30,67 €
PT820-21-45	21	129	129,26	45	0,4	30,67 €
PT820-23-25	23	141	141,22	25	0,5	32,38 €
PT820-23-30	23	141	141,22	30	0,5	32,38 €
PT820-23-35	23	141	141,22	35	0,5	32,38 €
PT820-23-40	23	141	141,22	40	0,5	32,38 €
PT820-23-45	23	141	141,22	45	0,5	32,38 €
PT820-25-25	25	153	153,20	25	0,5	32,71 €
PT820-25-30	25	153	153,20	30	0,5	32,71 €
PT820-25-35	25	153	153,20	35	0,5	32,71 €
PT820-25-40	25	153	153,20	40	0,5	32,71 €
PT820-25-45	25	153	153,20	45	0,5	32,71 €

Dimensions in mm

Our other products



CHM90

Worm and wheel gear reducer, up to 540 Nm



PSG25

Spur gear - precision range, Pre-hardened Steel 35NCD6



CHTRB

Single and dual output gearboxes, Up to 53,1 Nm



CHAGC-AL

Screw-in garnet hinge, Screw-on



M0

Worm and wheel set, Non hardened steel



AT5M AT10M

AT type timing belt per metre, AT10 Steel cored polyurethane



SBF

Sealed flange bearing unit for Food Industry, cover



BPM_LOK

Long-Lok slotted spring plunger with ball tip, LONG-LOK - Stainless ...



BABpss

301 Stainless steel ball pin, Stainless steel



TPEf

Castor for aluminium profile, Fixed



SH0

Parallel axis helical gear, Steel 20NCD2



AT5M AT10M

AT type timing belt per metre, AT5 Steel cored polyurethane

Complementary products



CAP820

Slim slat top chain acetal, Narrow straight range 820



CAP815

Slim slat top chain stainless steel, Narrow range 815



DBL820

Idler for slat top chain, Ranges 820 and 815



BAP25

Plastic clamping collar, Ø25 - Ø40