


- For driving CAP820 and CAP815 plate chains
- With bore and keyway
- Materials:
  - Reinforced polyamide
  - Stainless steel screws
- Operating temp.: -10°C to +120°C
- For dimensions and bore tolerances, please refer to technical pages


### Advantage

- Two part design facilitates easy assembly

Easy assembly



Two part design



### DISCOUNTS

Qty	1+	5+	10+
Disc.	List	-5%	On request

Part number	No. of teeth	ØDE	ØDP	Bore ØA	Weight (kg)	Price each 1 to 4
PT820-21-25	21	129	129,26	25	0,4	30,67 €
PT820-21-30	21	129	129,26	30	0,4	30,67 €
PT820-21-35	21	129	129,26	35	0,4	30,67 €
PT820-21-40	21	129	129,26	40	0,4	30,67 €
PT820-21-45	21	129	129,26	45	0,4	30,67 €
PT820-23-25	23	141	141,22	25	0,5	32,38 €
PT820-23-30	23	141	141,22	30	0,5	32,38 €
PT820-23-35	23	141	141,22	35	0,5	32,38 €
PT820-23-40	23	141	141,22	40	0,5	32,38 €
PT820-23-45	23	141	141,22	45	0,5	32,38 €
PT820-25-25	25	153	153,20	25	0,5	32,71 €
PT820-25-30	25	153	153,20	30	0,5	32,71 €
PT820-25-35	25	153	153,20	35	0,5	32,71 €
PT820-25-40	25	153	153,20	40	0,5	32,71 €
PT820-25-45	25	153	153,20	45	0,5	32,71 €

Dimensions in mm

## Our other products



RCC\_RCX

Spherical tilt washer -  
DIN6319, concave



RCX-6

Spherical tilt washer -  
DIN6319, convex



HTD5M\_09

HTD Heavy duty  
timing pulley, HTD5  
Steel



MFB\_MHB

Moulded plastic bevel  
gear (nylon), 4:1



VTA

Vari-Tork® slip  
friction clutch, 0.53 to  
1.32 Nm



HTD8M\_30

HTD Heavy duty  
timing pulley, HTD8  
Cast



RAGb

Cylindrical brush  
track, For gentle  
conveying and  
handling



PCS25ECO

Chain sprocket - steel,  
6.35mm




CHAEss

Decorative hinge,  
Stainless steel



BLH40

Right angled gearbox,  
from 3 to 10.30 Nm



T5M T10M

T type timing belt per  
metre, T10 Steel  
cored polyurethane



PPJ

Indexing plunger with  
flange, With  
horizontal mounting  
flange and pu...

## Complementary products



CAP820

Slim slat top chain  
acetal, Narrow  
straight range 820



CAP815

Slim slat top chain  
stainless steel,  
Narrow range 815



DBL820

Idler for slat top  
chain, Ranges 820  
and 815



BAP25

Plastic clamping  
collar, Ø25 - Ø40