

- For driving CAP881T/SS chains
- With bore and keyway
- Materials:
 - Reinforced polyamide
 - Stainless steel screws
- Operating temp.: -10°C to +120°C
- For dimensions and bore tolerances, please refer to technical pages


Advantage

- Two part design facilitates easy assembly

Easy assembly



Two part design



DISCOUNTS

Qty	1+	5+	10+
Disc.	List	-5%	On request

Part number	No. of teeth	ØDE	ØDP	Bore ØA	Weight (kg)	Price each 1 to 4
PT881-21-25	21	129	129,26	25	0,37	29,91 €
PT881-21-30	21	129	129,26	30	0,37	29,91 €
PT881-21-35	21	129	129,26	35	0,37	29,91 €
PT881-21-40	21	129	129,26	40	0,37	29,91 €
PT881-21-45	21	129	129,26	45	0,37	29,91 €
PT881-23-25	23	141	141,22	25	0,44	31,05 €
PT881-23-30	23	141	141,22	30	0,44	31,05 €
PT881-23-35	23	141	141,22	35	0,44	31,05 €
PT881-23-40	23	141	141,22	40	0,44	31,05 €
PT881-23-45	23	141	141,22	45	0,44	31,05 €
PT881-25-25	25	153	153,20	25	0,49	32,61 €
PT881-25-30	25	153	153,20	30	0,49	32,61 €
PT881-25-35	25	153	153,20	35	0,49	32,61 €
PT881-25-40	25	153	153,20	40	0,49	32,61 €
PT881-25-45	25	153	153,20	45	0,49	32,61 €

Dimensions in mm

Our other products



Single chain supplied by the metre, Steel



Jaw coupling, economy range, Aluminium



Strike for toggle latch, 25.5mm



Anti-vibration machine mount, Oval base plate



Moulded plastic bevel gear (nylon), 1:1



Right angled gearbox, double output shafts, up to 30 Nm



Spur gear - precision range, Pre-hardened Steel 35NCD6



Worm and wheel set, Bronze



Closing mechanism for aluminium profile,



Coupling bar for aluminium profile,



Bellows coupling Gerwah®, from 0.5 to



Articulated foot Ø103, Ø 103

Complementary products



Side flexing slim slat top chain stainless steel, Narrow range 881



Asynchronous AC motorgearboxes 0.09 to 0.22kW, 0.09 to 0.22kW



Shaft for worm and wheel reducer CHMR and CHM, CHMR and CHM gearbox...