

Anti-vibration machine mount


New

PMB

Format Oval base plate

- With 2 fixing holes
- Loads shown refer to permissible static vertical dead load
- Materials :
 - Natural rubber
 - Steel structure

NEW !






Application

- These elements are ideal for low frequencies because the rubbers are available with different hardnesses so that a wide load range can be covered

Info.

- Supplied with support disc for better load distribution



DISCOUNTS

Qty	1+	6+	10+	20+
Disc.	List	-5%	-10%	On request

Part number	ØD	H1	H	E	L	ØM	ØA	S	Hardness shore	Load max (daN)	Deflexion	Price each 1 to 5
PMB40-M6-35	40	18	20	52	64	M6	6,2	2	35	2,5	2,5±0,5	9,83 €
PMB40-M6-45	40	18	20	52	64	M6	6,2	2	45	5	2,5±0,5	9,83 €
PMB40-M6-60	40	18	20	52	64	M6	6,2	2	60	10	2,5±0,5	9,83 €
PMB60-M6-45	60	22	24	76	90	M6	6,2	2	45	15	3,5±0,5	17,04 €
PMB60-M6-60	60	22	24	76	90	M6	6,2	2	60	25	3,5±0,5	17,04 €
PMB60-M6-75	60	22	24	76	90	M6	6,2	2	75	50	3,5±0,5	17,04 €
PMB80-M8-45	80	25	27	100	120	M8	8,2	2	45	40	4,5±0,5	23,19 €
PMB80-M8-60	80	25	27	100	120	M8	8,2	2	60	80	4,5±0,5	23,19 €
PMB80-M8-75	80	25	27	100	120	M8	8,2	2	75	120	4,5±0,5	23,19 €
PMB100-M10-45	100	25	28	124	148	M10	10,2	2,5	45	75	4,5±1	30,37 €
PMB100-M10-60	100	25	28	124	148	M10	10,2	2,5	60	160	4,5±1	30,37 €
PMB100-M10-75	100	25	28	124	148	M10	10,2	2,5	75	220	4,5±1	30,37 €
PMB150-M14-45	150	35	40	182	214	M14	11,8	4	45	130	7±1,5	66,64 €
PMB150-M14-60	150	35	40	182	214	M14	11,8	4	60	300	7±1,5	66,64 €
PMB150-M14-75	150	35	40	182	214	M14	11,8	4	75	400	7±1,5	66,64 €

Dimensions in mm

HPC

WEB
04/2024

www.hpceurope.com

Tel. +33(0)4 37 496 496

Our other products



PSG125S

Spur gear - precision range, Stainless steel 316



CHTRP

Single and dual output gearboxes, Up to 75,7 Nm



G01

Single universal joint, Normal duty



TCXR

Automatic chain tensioner, With stainless steel sprocket



DOMI30

Accessories, Plate



DBL821

Idler for slat top chain, Range 821



ACLBDB

Closing mechanism for aluminium profile, Dual ball catch



BC2

Panamech, Multi-Beam, Aluminium - with clamping jaw



BLM

Spring loaded plunger with ball tip, Stainless steel body



APBC

Circular rod, Round rod



PPOss

Pad eye on mounting plate oval, Stainless steel



PSG1S

Spur gear - precision range, Stainless steel 303

Complementary products



AZY

Cylindrical elasto mount, Steel



AZY_SS

Stainless steel cylindrical elasto mount, Stainless steel



BZY

Cylindrical elasto mount, Steel



BZY_SS

Stainless steel cylindrical elasto mount, Stainless steel