

Stainless steel swivelling foot



PTKss **A**
3

Max load 25,000N

- "Teknohygienic" swivelling foot

- Materials:

Base: stainless steel 304

Stem: stainless steel 304


Sole: NBR rubber Shore hardness 90°

Advantages

- The 3-A standard designates products that are designed for the dairy, food and pharmaceutical industries where strict hygiene rules apply.
- Smooth finished foot with a wiper seal between the stem and the nut and around the swivel to prevent accumulation of dirt or retention of water
- Suitable for cleaning with water or chemicals
- USDA approved

For the food industry
stainless steel

Avoids water retention



DISCOUNTS

Qty	1+	6+	10+
Disc.	List	-5%	On request

Part number	ØM	Adju- stable range E	A	B	ØD	SW	ØD1	ØD2	G	CH	H1	H2	H3	Static load (N)	Price each 1 to 5
PTK80-16-140/SS	M16	45	53	140	80	13	24	60	25	20	193	114	159	20000	84,11 €
PTK80-16-190/SS	M16	70	53	190	80	13	24	85	25	20	243	139	209	20000	100,98 €
PTK80-20-140/SS	M20	45	53	140	80	17	30	60	25	26	193	114	159	20000	88,33 €
PTK80-20-142/SS	M20	55	53	142	80	17	30	70	25	26	195	123	178	20000	91,25 €
PTK80-20-190/SS	M20	70	53	190	80	17	30	85	25	26	243	139	209	20000	101,89 €
PTK80-24-140/SS	M24	45	53	140	80	20	35	60	25	30	193	114	159	20000	96,03 €
PTK80-24-190/SS	M24	70	53	190	80	20	35	85	25	30	243	139	209	20000	108,86 €
PTK100-16-140/SS	M16	45	56	140	100	13	24	60	28	20	196	117	162	25000	88,14 €
PTK100-16-190/SS	M16	70	56	190	100	13	24	85	28	20	246	142	212	25000	105,01 €
PTK100-20-140/SS	M20	45	56	140	100	17	30	60	28	26	196	117	162	25000	92,37 €
PTK100-20-190/SS	M20	70	56	190	100	17	30	85	28	26	246	142	212	25000	105,91 €
PTK100-24-140/SS	M24	45	56	140	100	20	35	60	28	30	196	117	162	25000	100,06 €
PTK100-24-190/SS	M24	70	56	190	100	20	35	85	28	30	246	142	212	25000	112,90 €
PTK100-30-135/SS	M30	40	56	135	100	26	42	60	28	36	191	117	157	25000	109,95 €
PTK100-30-185/SS	M30	65	56	185	100	26	42	85	28	36	241	142	207	25000	120,20 €

Dimensions in mm

HPC

WEB
04/2020

www.hpceurope.com

Tél: 0 825 88 5000 Service 0,15 €/min + prix appel

Our other products



Q6

Deep groove ball bearing, Steel



MEFC

Flanged sintered ferrous bush, Self-lubricating FP20 ferrous alloy M...



UGH32

H Type Guide units, For Ø32 actuators



BLH60

Right angled gearbox, from 19 to 70 Nm



BPPL

Mini plain bearing ball transfer unit, For countersinking



M1

Worm and wheel set, Non hardened steel



GCT

Pipe lynch pin, Tube lynch pin



ACLBDB

Closing mechanism for aluminium profile, Dual ball catch



BAC105

Storage bin, 8mm



GPLss

Brush, stainless steel



CHALss

Piano hinge, Stainless steel



BOXdh

Boxed set of cylindrical dowel pins DIN6325, Boxed set - Solid DIN 6...

Complementary products



PTKFss

Fixable foot for the food industry, Stainless steel - 3-A standard



PTA80

Articulated levelling foot, pressed base Ø80, Ø 80



PTA80

Articulated levelling foot, pressed base Ø80, Ø 80



PTA100

Articulated levelling foot, pressed base Ø100, Ø 100