

Stainless steel swivelling foot



PTKss **A**
3

Max load 25,000N

- "Teknohygienic" swivelling foot

- Materials:

Base: stainless steel 304

Stem: stainless steel 304


Sole: NBR rubber Shore hardness 90°

Advantages

- The 3-A standard designates products that are designed for the dairy, food and pharmaceutical industries where strict hygiene rules apply.
- Smooth finished foot with a wiper seal between the stem and the nut and around the swivel to prevent accumulation of dirt or retention of water
- Suitable for cleaning with water or chemicals
- USDA approved

For the food industry
stainless steel

Avoids water retention



DISCOUNTS

Qty	1+	6+	10+
Disc.	List	-5%	On request

Part number	ØM	Adju- stable range E	A	B	ØD	SW	ØD1	ØD2	G	CH	H1	H2	H3	Static load (N)	Price each 1 to 5
PTK80-16-140/SS	M16	45	53	140	80	13	24	60	25	20	193	114	159	20000	84,11 €
PTK80-16-190/SS	M16	70	53	190	80	13	24	85	25	20	243	139	209	20000	100,98 €
PTK80-20-140/SS	M20	45	53	140	80	17	30	60	25	26	193	114	159	20000	88,33 €
PTK80-20-142/SS	M20	55	53	142	80	17	30	70	25	26	195	123	178	20000	91,25 €
PTK80-20-190/SS	M20	70	53	190	80	17	30	85	25	26	243	139	209	20000	101,89 €
PTK80-24-140/SS	M24	45	53	140	80	20	35	60	25	30	193	114	159	20000	96,03 €
PTK80-24-190/SS	M24	70	53	190	80	20	35	85	25	30	243	139	209	20000	108,86 €
PTK100-16-140/SS	M16	45	56	140	100	13	24	60	28	20	196	117	162	25000	88,14 €
PTK100-16-190/SS	M16	70	56	190	100	13	24	85	28	20	246	142	212	25000	105,01 €
PTK100-20-140/SS	M20	45	56	140	100	17	30	60	28	26	196	117	162	25000	92,37 €
PTK100-20-190/SS	M20	70	56	190	100	17	30	85	28	26	246	142	212	25000	105,91 €
PTK100-24-140/SS	M24	45	56	140	100	20	35	60	28	30	196	117	162	25000	100,06 €
PTK100-24-190/SS	M24	70	56	190	100	20	35	85	28	30	246	142	212	25000	112,90 €
PTK100-30-135/SS	M30	40	56	135	100	26	42	60	28	36	191	117	157	25000	109,95 €
PTK100-30-185/SS	M30	65	56	185	100	26	42	85	28	36	241	142	207	25000	120,20 €

Dimensions in mm



WEB
04/2020


www.hpceurope.com

Tél: 0 825 88 5000 Service 0,15 €/min + prix appel

Our other products



D-PAR_SS
Stainless steel
progressive stop,
stainless steel



M2
Worm and wheel set,
Bronze



GG3
Ground spur gear,
Heat treated steel



VCMB
Dual-thread screw
wood/metal, Stainless
steel



PRF_BR
Clamp for aluminium
profile, Clamp for
profile



T5P_T10P
Connecting plate for T
type timing belts, T5



BABpss
301 Stainless steel
ball pin, Stainless
steel




RHTpss
High Temperature
Castor, up to 200kg



SDB
Locking bolt support
bracket, Mounting
holes at 90° to
locating bolt



JSM
Cylindrical polymer
bush, Universal
polymer



AC
Strike for toggle latch,
15mm



LWL
Linear ball slide -
Stainless steel balls,
Rail - from 514 N to
1670...

Complementary products



PTKFss
Fixable foot for the
food industry,
Stainless steel - 3-A
standard



PTA80
Articulated levelling
foot, pressed base
Ø80, Ø 80



PTA80
Articulated levelling
foot, pressed base
Ø80, Ø 80



PTA100
Articulated levelling
foot, pressed base
Ø100, Ø 100