

# PERIFLEX® elastic coupling

## PNA

## Replacement tyre

### - Tyre for PERIFLEX® coupling

- Replace the tyre without dismantling the machine
- Material natural rubber Tyre R (NR) equipped with disposed material in R
- Quality tyre X(1) with inserts mounted in X pattern

### Assembly

- The elastic coupling is delivered pre-assembled. To mount the coupling, remove the tyre and place the hubs and locking assemblies on their respective shafts. Bring the two assemblies together respecting the distance "O" and aligning the two hubs with a straight edge or template.
- Place the tyre between the two hubs ensuring there is minimum radial backlash (2-15mm depending on the size of the coupling). Then bring the two locking assemblies together, tightening pairs of diametrically opposite screws to the prescribed torque. As the rubber may decompress with time, re-check the torque after a few hours.



**SAVE MONEY !**  
Only change the tyre


### DISCOUNTS

| Qty   | 1+   | 5+  | 10+        |
|-------|------|-----|------------|
| Disc. | List | -3% | On request |

| Part number spare tyre | for PERIFLEX® coupling part number | Type of tyre | Stock* | Price each 1 to 4 |
|------------------------|------------------------------------|--------------|--------|-------------------|
| 203R                   | PNA2-203                           | R            | -      | 92,88 €           |
| 206R                   | PNA6-206                           | R            | ✓      | 113,52 €          |
| 210R                   | PNA16-210                          | R            | ✓      | 171,31 €          |
| 214R                   | PNA40-214                          | R            | ✓      | 266,28 €          |
| 218R                   | PNA63-218                          | R            | ✓      | 276,60 €          |
| 414X                   | PNA40-214                          | X            | -      | 268,36 €          |
| 418X                   | PNA63-218                          | X            | -      | 295,18 €          |

\*Depending on availability - Dimensions in mm

## Our other products



QNUP  
Single row cylindrical roller bearing, 1 fixed inner flange and 1 fr...



CABPVC  
PVC covered galvanised steel cable, Galvanised steel with



PLM-16A  
Magnetic stud with threaded hole, With threaded hole



KKSS  
Rounded end feather key, Stainless steel



SCA  
Flat cable clamp, Steel



PSG25  
Spur gear - precision range, Stainless steel 316



COA-COG  
Surface mounting plate, Surface mounting plate for ball joint



PMC48\_M8  
Anti-vibration machine mount, Oval base plate



BL8  
Right angled gearbox, from 0.20 to 2 Nm



PSG055  
Spur gear - precision range, Stainless steel 316



MEB  
Moulded plastic bevel gear (nylon), 1:1



AZY\_SS  
Stainless steel cylindrical elastomeric mount, Stainless steel

## Complementary products



PNA  
PERIFLEX® elastic coupling, Complete coupling