

# Universal threaded lifting hook

Base rotates through 360°

**RUD** PPS



- **Universal lifting hook for all applications.**
- Suitable for use with cables, round or synthetic slings and chains
- Double ball bearings allows for loads to turn or tilt
- Visual overload indication on hook
- Hook and latched manufactured from forged steel and 100% crack tested
- Hook has a pink thermochromic finish (High visibility)

## Option

- Can be supplied with a longer thread and nut for use with a through hole or for mounting on lighter metals such as aluminium

## Info

- Conforms to EU Directive 98/37/CE
- Load capacity doesn't change with load direction



**4** Suitable for lifting in any direction  
Factor of safety = 4

CE

## DISCOUNTS

Qty	1+	5+	10+	15+
Disc.	List -3%	-6%	On request	

Part number	Load		A	B	C	D	SW	F	G	E	Weight (kg)	Torque de serrage (Nm)	Price each
	CMU (t)	ØM											
PPS-M12	0,63	M12	13	75	18	40	36	18	41	116	0,4	10	137,17 €
PPS-M16	1,5	M16	20	97	25	46	41	24	50	146	0,9	30	172,68 €
PPS-M20	2,5	M20	28	126	30	61	55	30	61	187	1,7	70	216,51 €
PPS-M24	4,0	M24	36	150	35	78	70	36	77	227	3,5	150	304,36 €
PPS-M30	5,0	M30	37	174	40	95	85	45	93	267	7,5	225	444,13 €
PPS-M36	8,0	M36	49	208	48	100	90	54	102	310	9,2	410	702,55 €

\*Depending on availability - Dimensions in mm


## Our other products



GE14  
Toggle latches, With padlock-holder



NDS20  
Double cross clamp, Parallel



GPLny  
Brush, nylon



PO  
Pull handle - Multi-sector, Tapped recessed insert



RHTplss  
High Temperature Castor, up to 200kg



SLVlok  
Vertical toggle clamp, Vertical toggle clamp / vertical foot



BMM  
Knurled knob - male, Knurled



CHAB  
Hinge with stop, Hinge



PRES  
Manual workbench press accessory for PRES-3HR end



PCS37  
Chain sprocket - steel, 9.525mm (DIN06B-1)



PRF\_PF  
Anchoring bracket for aluminium profile, Anchor



BSP  
Compact precision slide, from 156 N to 980 N

## Complementary products



VRSSs  
Male swivelling lifting rings stainless steel, Male swivelling - s...



WBGV  
Lifting ring, Threaded



VRSF  
Male swivelling lifting ring, Male swivelling



VRM  
Female swivelling lifting rings, Female swivelling