


- **Levelling foot**
- Non slip base
- **Materials:**
 - Base: Black glass reinforced polyamide (Shore 70)
 - Spindle: Zinc plated steel or stainless 304 (nut not supplied)

Info.

- Values given for static loads will be reduced in case of a vibrating load



With non-slip base



DISCOUNTS

| | | | |
|--------------|-----------|------------|-----|
| Qty | 1+ | 20+ | 50+ |
| Disc. | List -10% | On request | |

| Part number | ØD | Thread ØF | B | A | A/F | G | H | H1 | Static load (N) | Price each | |
|--------------------------------|-----|-----------|-----|----|-----|----|-----|-----|-----------------|------------|---------|
| | | | | | | | | | | Stock* | 1 to 19 |
| Steel spindle | | | | | | | | | | | |
| PR105-16-75 | 103 | M16 | 75 | 51 | 20 | 32 | 126 | 129 | 25000 | ✓ | 17,76 € |
| PR105-16-150 | 103 | M16 | 150 | 51 | 20 | 32 | 201 | 204 | 25000 | ✓ | 21,36 € |
| PR105-16-225 | 103 | M16 | 225 | 51 | 20 | 32 | 276 | 279 | 25000 | ✓ | 26,31 € |
| PR105-20-125 | 103 | M20 | 125 | 51 | 20 | 32 | 176 | 179 | 25000 | ✓ | 17,99 € |
| PR105-20-200 | 103 | M20 | 200 | 51 | 20 | 32 | 251 | 254 | 25000 | ✓ | 21,34 € |
| PR105-20-250 | 103 | M20 | 250 | 51 | 20 | 32 | 301 | 304 | 25000 | ✓ | 26,31 € |
| PR105-24-125 | 103 | M24 | 125 | 51 | 20 | 32 | 176 | 179 | 25000 | ✓ | 17,99 € |
| PR105-24-200 | 103 | M24 | 200 | 51 | 20 | 32 | 251 | 254 | 25000 | ✓ | 21,34 € |
| PR105-24-250 | 103 | M24 | 250 | 51 | 20 | 32 | 301 | 304 | 25000 | ✓ | 26,31 € |
| Stainless steel spindle | | | | | | | | | | | |
| PR105-16-75/SS | 103 | M16 | 75 | 51 | 20 | 32 | 126 | 129 | 25000 | ✓ | 31,56 € |
| PR105-16-150/SS | 103 | M16 | 150 | 51 | 20 | 32 | 201 | 204 | 25000 | ✓ | 41,75 € |
| PR105-16-225/SS | 103 | M16 | 225 | 51 | 20 | 32 | 276 | 279 | 25000 | ✓ | 53,74 € |
| PR105-20-125/SS | 103 | M20 | 125 | 51 | 20 | 32 | 176 | 179 | 25000 | ✓ | 36,50 € |
| PR105-20-200/SS | 103 | M20 | 200 | 51 | 20 | 32 | 251 | 254 | 25000 | ✓ | 50,12 € |
| PR105-20-250/SS | 103 | M20 | 250 | 51 | 20 | 32 | 301 | 304 | 25000 | ✓ | 58,20 € |
| PR105-24-125/SS | 103 | M24 | 125 | 51 | 20 | 32 | 175 | 178 | 25000 | - | 36,50 € |
| PR105-24-200/SS | 103 | M24 | 200 | 51 | 20 | 32 | 250 | 253 | 25000 | - | 50,12 € |
| PR105-24-250/SS | 103 | M24 | 250 | 51 | 20 | 32 | 300 | 303 | 25000 | - | 58,20 € |

*Depending on availability - Dimensions in mm

Our other products



PSG125

Spur gear - precision range, Pre-hardened Steel 35NCD6



CDGamme

Compression spring
DIN2095, DIN 2095



PDD

Spring plunger, With
sensor adaptor



G1

Steel spur gear, Steel
20NCD2



PM2

Worm and wheel set,
Hardened steel




CLQassortiment

Assorted feeler strips,
Assorted feeler strips



HLUMss

Revolving handle for
handwheel, Stainless
steel 316



AC

Strike for toggle latch,
18mm



MCL

Cylindrical threaded
sleeve, Cylindrical -
steel



TBD

Manual leadscrew
table with opposing
threads, 5kg



SHSS

Shoulder screw
stainless steel 416,
Pre-treated 416



BABS303

303 Stainless steel
compact ball pin,
Stainless steel 303

Complementary products



PR65C

Half-articulated foot Ø
65, Ø 65