

PW PSW Worm and wheel set

Worm available in pre-treated or **stainless steel**

Module 2,0



- Quality grade 7e25 DIN 3974
- Pressure angle: 20°
- Material:
 - Pre-treated steel 35NCD6, 28HRC
 - Stainless steel 303
- Tooth thickness conforms to DIN 3967



Quality grade 7e25

Info.

- Torque figures are for 100 rpm and are given as a guide only.



DISCOUNTS

Qty	1+	6+	19+	50+
Disc.	List	-5%	-10%	On request

Part number		No of starts	Price each 1 to 5	
Steel	Stainless steel		Steel	Stainless steel
Bored worm				
PW2.0-1	PW2.0-1S	1	99,63 €	134,53 €
PW2.0-2	PW2.0-2S	2	99,63 €	134,53 €
PW2.0-3	PW2.0-3S	3	99,63 €	134,53 €
PW2.0-4	PW2.0-4S	4	99,63 €	134,53 €
Shaft worm				
PSW2.0-1	PSW2.0-1S	1	151,11 €	204,01 €
PSW2.0-2	PSW2.0-2S	2	151,11 €	204,01 €
PSW2.0-3	PSW2.0-3S	3	151,11 €	204,01 €
PSW2.0-4	PSW2.0-4S	4	151,11 €	204,01 €

Dimensions in mm

Worm and wheel set

PWG

Bronze wheel

Module
2,0


- Quality grade 7e25 DIN 3974
- Pressure angle: 20°
- Material: Bronze CA104 (CuAl10Ni5Fe4)
- Tooth thickness conforms to DIN 3967

Options

- Alternative bores (H7)
- Keyway conforming to DIN6885 (JS9)
- Tapped hole
- Hole for dowel pin

Info.

- Torque figures are for 100 rpm and are given as a guide only.
- To order, add the number of starts to the part number:
e.g. worm PW2,0-4, wheel PWG2,0-15-4



DISCOUNTS

Qty	1+	6+	19+	50+
Disc.	List	-5%	-10%	On request

Part number	No of teeth	a	ØD	ØDa	ØDe	Bore ØA	ØM	Theoretical backlash (mm)		Torque (Nm)	Price each 1 to 5
								Max.	Min.		
PWG2,0-15-1	15	27,50	30	34	36	10	25	0,114	-0,040	11,30	175,59 €
PWG2,0-16-1	16	28,50	32	36	38	10	25	0,114	-0,040	12,69	185,62 €
PWG2,0-17-1	17	29,50	34	38	40	10	25	0,114	-0,040	14,16	189,13 €
PWG2,0-18-1	18	30,50	36	40	42	10	25	0,117	-0,038	15,69	192,68 €
PWG2,0-19-1	19	31,50	38	42	44	10	25	0,117	-0,038	17,30	196,32 €
PWG2,0-20-1	20	32,50	40	44	46	10	25	0,117	-0,038	19,29	199,86 €
PWG2,0-21-1	21	33,50	42	46	48	12	35	0,117	-0,038	21,06	211,10 €
PWG2,0-22-1	22	34,50	44	48	50	12	35	0,117	-0,038	23,27	223,76 €
PWG2,0-23-1	23	35,50	46	50	52	12	35	0,117	-0,038	25,62	230,01 €
PWG2,0-24-1	24	36,50	48	52	54	12	35	0,117	-0,038	28,09	235,82 €
PWG2,0-25-1	25	37,50	50	54	56	12	35	0,117	-0,038	30,24	241,98 €
PWG2,0-26-1	26	38,50	52	56	58	12	35	0,137	-0,048	32,45	247,89 €
PWG2,0-27-1	27	39,50	54	58	60	12	35	0,137	-0,048	34,73	249,82 €
PWG2,0-28-1	28	40,50	56	60	62	12	35	0,137	-0,048	37,08	253,86 €
PWG2,0-29-1	29	41,50	58	62	64	14	50	0,137	-0,048	39,50	257,87 €
PWG2,0-30-1	30	42,50	60	64	66	14	50	0,137	-0,048	41,98	259,87 €
PWG2,0-32-1	32	44,50	64	68	70	14	50	0,137	-0,048	47,15	269,86 €
PWG2,0-35-1	35	47,50	70	74	76	14	50	0,137	-0,048	55,41	316,77 €
PWG2,0-38-1	38	50,50	76	80	82	14	50	0,139	-0,045	64,25	367,39 €
PWG2,0-40-1	40	52,50	80	84	86	14	50	0,139	-0,045	70,46	403,23 €
PWG2,0-42-1	42	54,50	84	88	90	14	50	0,139	-0,045	76,93	440,79 €
PWG2,0-45-1	45	57,50	90	94	96	14	50	0,139	-0,045	88,46	500,08 €
PWG2,0-48-1	48	60,50	96	100	102	14	50	0,139	-0,045	99,36	559,87 €
PWG2,0-50-1	50	62,50	100	104	106	16	65	0,139	-0,045	106,94	603,63 €
PWG2,0-52-1	52	64,50	104	108	110	16	65	0,139	-0,045	114,76	649,28 €
PWG2,0-55-1	55	67,50	110	114	116	16	65	0,139	-0,045	126,95	713,80 €
PWG2,0-58-1	58	70,50	116	120	122	16	65	0,139	-0,045	139,68	788,30 €
PWG2,0-60-1	60	72,50	120	124	126	16	65	0,139	-0,045	153,04	839,98 €

Wheels available with 15 to 60 teeth

Dimensions in mm

Our other products



RJA11_27

Sealing strip, Not clipping



AC144

Strike for toggle latch, 22mm



PRF JL6

Lip seal for panel, Door seal - Ø 6mm



PRF_ART

Articulated bracket for use with aluminium profile, With clamping ha...




GG2

Ground spur gear, Heat treated steel



MHPGR

Arm with folding rotating handle,



TBV

Manual lifting tables, 12kg



GE1006

Elastic ringed latch, Hooks into a slot



TBD

Manual leadscrew table with opposing threads, 20kg



YG1

HEAVY DUTY spur gear, Steel 35NCD6



AFSE

Locking pin with interlocking safety latch, with interlocking safety...



BPMc

Stainless steel slotted spring plunger with ceramic ball tip, 303 St...

Complementary products



PW_PWG2

Worm - precision range, Steel



PW_PWG2

Wheel - precision range, Bronze