Fixable articulated foot Ø40 and Ø50

PR40
PR50

Accepts loads up to 11,000N

- ***Levelling foot***
- *Rubber anti-slip sole (NBR 70 Shore)*
- *Black glass fibre reinforced Polyamide base*
- *Threaded ball ended spindle in plated steel or stainless steel*
- *Nut not supplied*

With non-slip sole




Advantages

- *Self aligning on floor due to use of ball ended rod*
- *Flexible and non-slip sole*

Info.

- *If subjected to vibration, the stati given will be reduced*



DISCOUNTS

Qty	1+	20+	50+
Disc.	List	-10%	On request

Part number	ØD	Thread ØF	B	A	A/F	G	H	H1	Static load (N)	Stock*	Price each 1 to 19
Steel spindle											
PR40-6-25	40	M6	25	27	12	16,5	52	55	5000	-	5,68 €
PR40-6-50	40	M6	50	27	12	16,5	77	80	5000	-	5,68 €
PR40-8-50	40	M8	50	27	12	16,5	77	80	10000	✔	6,31 €
PR40-8-100	40	M8	100	27	12	16,5	127	130	10000	✔	8,74 €
PR50-10-75	50	M10	75	30	14	20,0	105	108	11000	✔	8,51 €
PR50-10-125	50	M10	125	30	14	20,0	155	158	11000	✔	10,15 €
PR50-12-75	50	M12	75	30	14	20,0	105	108	11000	✔	9,34 €
PR50-12-125	50	M12	125	30	14	20,0	155	158	11000	✔	10,43 €
PR50-16-75	50	M16	75	30	16	20,0	105	108	11000	-	10,54 €
PR50-16-125	50	M16	125	30	16	20,0	155	158	11000	-	11,81 €
Stainless steel spindle											
PR40-6-25/SS	40	M6	25	27	12	16,5	52	55	5000	-	8,56 €
PR40-6-50/SS	40	M6	50	27	12	16,5	77	80	5000	-	10,82 €
PR40-8-50/SS	40	M8	50	27	12	16,5	77	80	10000	✔	11,83 €
PR40-8-100/SS	40	M8	100	27	12	16,5	127	130	10000	✔	16,86 €
PR50-10-75/SS	50	M10	75	30	14	20,0	105	108	11000	✔	15,76 €
PR50-10-125/SS	50	M10	125	30	14	20,0	155	158	11000	✔	19,40 €
PR50-12-75/SS	50	M12	75	30	14	20,0	105	108	11000	✔	14,51 €
PR50-12-125/SS	50	M12	125	30	14	20,0	155	158	11000	✔	17,73 €
PR50-16-75/SS	50	M16	75	30	16	20,0	105	108	11000	-	16,07 €
PR50-16-125/SS	50	M16	125	30	16	20,0	155	158	11000	-	18,91 €


**Depending on avaibility- Dimensions in mm*

Half-articulated foot Ø65


Maximum load 18000N

PR65C

Swivel levelling foot with protective collar
- *Up to +/-8° from vertical*
- *Non slip base in NBR rubber 70 shore*
- *Base: Blue polyamide (RAL5005) fiber glass reinforced*
- *Spindle: Stainless steel 304*



Advantages
- *Articulated rod allows auto-alignment with the ground*
- *Sole material ensures flexibility and grip*
- *The collar at the base of the stem limits (but does not prevent) the retention of material*



DISCOUNTS

Qty	1+	20+	50+
Disc.	List	-10%	On request

Part number	ØD	Thread ØF	B	A	A/F	G	H	H1	Static load (N)	Price each 1 to 19
PR65C-12-50/SS	65	M12	50	39	10	29	89	92	13000	12,45 €
PR65C-12-100/SS	65	M12	100	39	10	29	139	142	13000	13,53 €
PR65C-12-150/SS	65	M12	150	39	10	29	189	192	13000	15,22 €
PR65C-16-100/SS	65	M16	100	39	13	29	139	142	18000	15,71 €
PR65C-16-150/SS	65	M16	150	39	13	29	189	192	18000	18,45 €
PR65C-16-200/SS	65	M16	200	39	13	29	239	242	18000	20,36 €
PR65C-20-100/SS	65	M20	100	41	17	29	141	144	18000	20,36 €
PR65C-20-150/SS	65	M20	150	41	17	29	191	194	18000	23,59 €
PR65C-20-200/SS	65	M20	200	41	17	29	241	244	18000	26,88 €
PR65C-20-250/SS	65	M20	250	41	17	29	291	294	18000	30,62 €

Dimensions in mm

Fixable articulated foot Ø83

Stock Ste Sta

PR85 Maximum load 20,000N

- **Levelling foot**
- Non slip base
- Materials:
  Base: Black glass reinforced polyamide (Shore 70)
  Spindle: Zinc plated steel or stainless 304 steel
- Supplied without nut





Advantages

- Articulated rod allows auto-alignment with the ground
- Sole material ensures flexibility and grip

Info.

- Values given for static, should will be reduced in case of a vibrating load





DISCOUNTS

Qty	1+	20+	50+
Disc.	List	-10%	On request

Part number	ØD	Thread ØF	B	A	A/F	G	H	H1	Static load (N)	Type	Stock*	Price each 1 to 19
Steel spindle												
PR85-12-75	83	M12	75	38	14	27	113	116	15000	H	✔	11,45 €
PR85-12-125	83	M12	125	38	14	27	163	166	15000	H	✔	12,79 €
PR85-16-75	83	M16	75	38	16	27	113	116	20000	H	✔	12,04 €
PR85-16-150	83	M16	150	38	16	27	188	191	20000	H	✔	14,16 €
PR85-16-200	83	M16	200	38	16	27	238	241	20000	H	✔	15,59 €
PR85-20-125	83	M20	125	41	17	27	166	169	20000	M	✔	13,11 €
PR85-20-175	83	M20	175	41	17	27	216	219	20000	M	✔	14,98 €
PR85-20-225	83	M20	225	41	17	27	266	269	20000	M	✔	17,02 €
Stainless steel spindle												
PR85-12-75/SS	83	M12	75	38	14	27	113	116	15000	H	✔	19,44 €
PR85-12-125/SS	83	M12	125	38	14	27	163	166	15000	H	✔	22,37 €
PR85-16-75/SS	83	M16	75	41	13	27	116	119	20000	M	✔	19,44 €
PR85-16-150/SS	83	M16	150	41	13	27	191	194	20000	M	✔	23,84 €
PR85-16-200/SS	83	M16	200	41	13	27	241	244	20000	M	✔	26,79 €
PR85-20-125/SS	83	M20	125	41	17	27	166	169	20000	M	✔	27,25 €
PR85-20-175/SS	83	M20	175	41	17	27	216	219	20000	M	✔	32,10 €
PR85-20-225/SS	83	M20	225	41	17	27	266	269	20000	M	⏳	38,79 €

*Depending on availability - Dimensions in mm

Fixable articulated foot Ø103

Maximum load 25,000N

PR105


- ***Levelling foot***
- *Non slip base*
- *Materials:*
  Base: Black glass reinforced polyamide (Shore 70)
  Spindle: Zinc plated steel or stainless 304 (nut not supplied)

With non-slip base



Info.

- *Values given for static loads will be reduced in case of a vibrating load*



DISCOUNTS

Qty	1+	20+	50+
Disc.	List	-10%	On request

Part number	ØD	Thread ØF	B	A	A/F	G	H	H1	Static load (N)	Stock*	Price each 1 to 19
Steel spindle											
PR105-16-75	103	M16	75	51	20	32	126	129	25000	✔	19,19 €
PR105-16-150	103	M16	150	51	20	32	201	204	25000	✔	23,08 €
PR105-16-225	103	M16	225	51	20	32	276	279	25000	✔	28,44 €
PR105-20-125	103	M20	125	51	20	32	176	179	25000	✔	19,44 €
PR105-20-200	103	M20	200	51	20	32	251	254	25000	✔	23,06 €
PR105-20-250	103	M20	250	51	20	32	301	304	25000	✔	28,44 €
PR105-24-125	103	M24	125	51	20	32	176	179	25000	✔	19,44 €
PR105-24-200	103	M24	200	51	20	32	251	254	25000	✔	23,06 €
PR105-24-250	103	M24	250	51	20	32	301	304	25000	-	28,44 €
Stainless steel spindle											
PR105-16-75/SS	103	M16	75	51	20	32	126	129	25000	✔	34,11 €
PR105-16-150/SS	103	M16	150	51	20	32	201	204	25000	✔	45,13 €
PR105-16-225/SS	103	M16	225	51	20	32	276	279	25000	✔	58,08 €
PR105-20-125/SS	103	M20	125	51	20	32	176	179	25000	-	39,45 €
PR105-20-200/SS	103	M20	200	51	20	32	251	254	25000	-	54,17 €
PR105-20-250/SS	103	M20	250	51	20	32	301	304	25000	✔	62,89 €
PR105-24-125/SS	103	M24	125	51	20	32	175	178	25000	-	39,45 €
PR105-24-200/SS	103	M24	200	51	20	32	250	253	25000	-	54,17 €
PR105-24-250/SS	103	M24	250	51	20	32	300	303	25000	-	62,89 €

**Depending on availability - Dimensions in mm*

Fixable articulated foot Ø123

Stock Ste Sta

PR125

Maximum load 35,000N

- ***Levelling foot***
- *Non slip base*
- *Materials:*
  Base: Black glass reinforced polyamide (Shore 70)
  Spindle: Zinc plated steel or stainless steel 304 (nut not supplied)

With non-slip base



Advantages


- *Articulated rod allows auto-alignment with the ground*
- *Sole material ensures flexibility and grip*

Accessories

- *Extension for articulated foot PR125-ENT* ***(p.27)***

Info.

- *Values given for static loads will be reduced in case of a vibrating load*



DISCOUNTS

Qty	1+	20+	50+
Disc.	List	-10%	On request

Part number	ØD	Thread ØF	B	A	A/F	G	H	H1	Static load (N)	Stock*	Price each 1 to 19
Steel spindle											
PR125-16-75	123	M16	75	57	20	37	132	133	35000	✔	22,33 €
PR125-16-150	123	M16	150	57	20	37	207	208	35000	✔	26,26 €
PR125-16-225	123	M16	225	57	20	37	282	285	35000	✔	30,70 €
PR125-20-125	123	M20	125	57	20	37	182	185	35000	✔	22,20 €
PR125-20-200	123	M20	200	57	20	37	257	260	35000	✔	25,93 €
PR125-20-250	123	M20	250	57	20	37	307	310	35000	✔	30,47 €
PR125-24-125	123	M24	125	57	20	37	182	185	35000	✔	22,20 €
PR125-24-200	123	M24	200	57	20	37	257	260	35000	✔	25,93 €
PR125-24-250	123	M24	250	57	20	37	307	310	35000	✔	30,47 €
PR125-30-125	123	M30	125	58	26	37	183	186	35000	✔	23,86 €
PR125-30-200	123	M30	200	58	26	37	258	261	35000	✔	28,53 €
PR125-30-250	123	M30	250	58	26	37	308	311	35000	-	31,75 €
Stainless steel spindle											
PR125-16-75/SS	123	M16	75	57	20	37	132	135	35000	-	38,49 €
PR125-16-150/SS	123	M16	150	57	20	37	207	210	35000	✔	49,45 €
PR125-16-225/SS	123	M16	225	57	20	37	282	285	35000	-	62,44 €
PR125-20-125/SS	123	M20	125	57	20	37	182	185	35000	✔	45,81 €
PR125-20-200/SS	123	M20	200	57	20	37	257	260	35000	-	58,54 €
PR125-20-250/SS	123	M20	250	57	20	37	307	310	35000	-	67,30 €
PR125-24-125/SS	123	M24	125	57	20	37	182	185	35000	-	45,81 €
PR125-24-200/SS	123	M24	200	57	20	37	257	260	35000	-	52,21 €
PR125-24-250/SS	123	M24	250	57	20	37	307	310	35000	-	67,30 €
PR125-30-125/SS	123	M30	125	58	26	37	183	186	35000	-	51,98 €
PR125-30-200/SS	123	M30	200	58	26	37	258	261	35000	-	66,37 €
PR125-30-250/SS	123	M30	250	58	26	37	308	311	35000	-	75,63 €

**Depending on availability - Dimensions in mm*


Extension for articulated foot Ø123

For articulated foot PR125 PR125


Extension with mounting holes for articulated feet PR125
- *Material*
  Polyamide
- *Delivered without anti-slip rubber pad*
- *Suitable for any type of floor*




Advantages
- *Easily compensates for large differences in floor level*



Assembly example
(screws not included)



Application example



DISCOUNTS

Qty	1+	20+	50+
Disc.	List	-10%	On request

Part number	ØD	ØE	H	ØG	ØF	Static load (N)	Price each 1 to 19
PR125-ENT	123	87	43	13	18	35000	13,71 €

Dimensions in mm