

# Fixable articulated foot Ø123

Stock Ste Sta

## PR125

## Maximum load 35,000N

- Levelling foot
- Non slip base
- Materials:  
Base: Black glass reinforced polyamide (Shore 70)  
Spindle: Zinc plated steel or stainless steel 304  
(nut not supplied)

### Advantages


- Articulated rod allows auto-alignment with the ground
- Sole material ensures flexibility and grip

### Accessories

- Extension for articulated foot  
PR125-ENT (p.27)

### Info.

- Values given for static loads will be reduced in case of a vibrating load



With non-slip base



### DISCOUNTS

Qty	1+	20+	50+
Disc.	List -10%	On request	

Part number	ØD	Thread	B	A	A/F	G	H	H1	Static load (N)	Price each 1 to 19
<b>Steel spindle</b>										
PR125-16-75	123	M16	75	57	20	37	132	133	35000	✓ 21,89 €
PR125-16-150	123	M16	150	57	20	37	207	208	35000	✓ 25,75 €
PR125-16-225	123	M16	225	57	20	37	282	285	35000	✓ 30,10 €
PR125-20-125	123	M20	125	57	20	37	182	185	35000	✓ 21,77 €
PR125-20-200	123	M20	200	57	20	37	257	260	35000	✓ 25,42 €
PR125-20-250	123	M20	250	57	20	37	307	310	35000	✓ 29,87 €
PR125-24-125	123	M24	125	57	20	37	182	185	35000	✓ 21,77 €
PR125-24-200	123	M24	200	57	20	37	257	260	35000	✓ 25,42 €
PR125-24-250	123	M24	250	57	20	37	307	310	35000	✓ 29,87 €
PR125-30-125	123	M30	125	58	26	37	183	186	35000	✓ 23,38 €
PR125-30-200	123	M30	200	58	26	37	258	261	35000	✓ 27,97 €
PR125-30-250	123	M30	250	58	26	37	308	311	35000	- 31,13 €
<b>Stainless steel spindle</b>										
PR125-16-75/SS	123	M16	75	57	20	37	132	135	35000	- 37,74 €
PR125-16-150/SS	123	M16	150	57	20	37	207	210	35000	✓ 48,48 €
PR125-16-225/SS	123	M16	225	57	20	37	282	285	35000	- 61,20 €
PR125-20-125/SS	123	M20	125	57	20	37	182	185	35000	✓ 44,91 €
PR125-20-200/SS	123	M20	200	57	20	37	257	260	35000	✓ 57,38 €
PR125-20-250/SS	123	M20	250	57	20	37	307	310	35000	- 65,97 €
PR125-24-125/SS	123	M24	125	57	20	37	182	185	35000	- 44,91 €
PR125-24-200/SS	123	M24	200	57	20	37	257	260	35000	- 51,18 €
PR125-24-250/SS	123	M24	250	57	20	37	307	310	35000	- 65,97 €
PR125-30-125/SS	123	M30	125	58	26	37	183	186	35000	- 50,96 €
PR125-30-200/SS	123	M30	200	58	26	37	258	261	35000	- 65,06 €
PR125-30-250/SS	123	M30	250	58	26	37	308	311	35000	- 74,14 €

\*Depending on availability - Dimensions in mm

# Extension for articulated foot Ø123

For articulated foot PR125


PR125

## Extension with mounting holes for articulated feet PR125


- Material  
Polyamide
- Delivered without anti-slip rubber pad
- Suitable for any type of floor

### Advantages


- Easily compensates for large differences in floor level



Assembly example  
(screws not included)



### Application example



### DISCOUNTS

Qty	1+	20+	50+
Disc.	List -10%	On request	

Part number	ØD	ØE	H	ØG	ØF	Static load (N)	Stock*	Price each 1 à 19
PR125-ENT	123	87	43	13	18	35000	-	13,44 €

\*Dans la limite du disponible - Dimensions en mm

## Our other products



T5-BAR  
T type tooth bar  
stock, T5



GAL\_25  
Ø25 conveyor roller,  
Without ball bearing



RESC  
Retractable castor for  
aluminium profile,  
Retractable castor



AT10courroie  
AT type timing belt,  
AT10 Steel cored  
polyurethane




UCP PBT  
Stainless/Polymer  
pillow block bearing,  
Polymer and stainless  
steel



NCT  
Square tube  
connector, Fixed  
angle




SH0  
Parallel axis helical  
gear, Steel 20NCD2



UCF PBT  
Stainless  
steel/Polymer flanged  
bearing, Polymer and  
stainless steel



VRBS  
Folding lifting ring for  
welding, Folding - for  
welding



LWH  
High rigidity linear  
slide, Chariot - from  
9320 N to 71300 N



AXTR  
Axle for tensioner  
pulley, Shaft



RURp  
Fixed castor with  
plate, Polyurethane -  
Aluminium rim (Free  
running)

## Complementary products



PR65C  
Half-articulated foot Ø  
65, Ø 65



PR125rehausse  
Extension for  
articulated foot Ø123,  
articulated foot PR125