

Self-aligning radial ball bearing

New

Q1
Q2

Steel

- Self aligning bearing that is unaffected by any errors in alignment

- Static and dynamic loads are radial loads

- Materials:

Rings and balls: steel

ETN9: Polyamide cage

ACC: Steel cage




DISCOUNTS

Qty	1+	4+	8+
Disc.	List	-15%	On request

Part number	Ød	ØD1	B	Load (kN)		Speed (rpm)		Weight (kg)	Price each 1 to 3
				Dynamic (C)	Static (Co)	Grease	Oil		
Q126-ETN9	6	19	6	2,460	0,470	34425	40500	0,009	3,54 €
Q1200-ETN9	10	30	9	5,420	1,160	27540	32400	0,034	3,36 €
Q1201-ETN9	12	32	10	6,120	1,400	24480	28800	0,040	3,51 €
Q2201-ETN9	12	32	14	8,350	1,860	22950	27000	0,053	5,01 €
Q1202-ETN9	15	35	11	7,260	1,720	21420	25200	0,049	3,82 €
Q2202-ETN9	15	35	14	8,540	2,000	19890	23400	0,060	4,46 €
Q2203-ETN9	17	40	12	8,660	2,160	18360	21600	0,073	3,94 €
Q2203-ETN9	17	40	16	10,390	2,500	18360	21600	0,088	4,06 €
Q1204-ETN9	20	47	14	12,450	3,330	15300	18000	0,120	5,59 €
Q2204-ETN9	20	47	18	16,460	4,070	15300	18000	0,140	5,84 €
Q1205-ACC	25	52	15	14,010	3,920	13770	16200	0,140	4,80 €
Q2205-ETN9	25	52	18	16,460	4,310	13770	16200	0,160	8,29 €
Q1305-ETN9	25	62	17	18,620	5,290	11475	13500	0,260	7,61 €
Q2305-ETN9	25	62	24	26,460	6,960	12240	14400	0,340	11,65 €
Q1206-ETN9	30	62	16	15,290	4,560	11475	13500	0,220	7,49 €
Q2206-ETN9	30	62	20	23,320	6,570	11475	13500	0,260	9,27 €
Q1306-ETN9	30	72	19	22,050	6,660	9945	11700	0,390	9,21 €
Q2306-ETN9	30	72	27	30,580	8,620	9945	11700	0,500	14,90 €
Q1207-ETN9	35	72	17	18,620	5,880	9945	11700	0,320	8,38 €
Q2207-ETN9	35	72	23	30,090	8,620	9180	10800	0,400	9,51 €
Q2307-ACC	35	80	21	25,970	8,330	8415	9900	0,510	11,78 €
Q1207-ACC	35	80	31	38,910	10,980	9180	10800	0,680	15,51 €

Dimensions in mm



DISCOUNTS

Qty	1+	4+	8+
Disc.	List	-15%	On request

Part number	Ød	ØD1	B	Load (kN)		Speed (rpm)		Weight (kg)	Price each 1 to 3
				Dynamic (C)	Static (Co)	lubricant Grease	Oil		
Q1208-ETN9	40	80	18	19,500	6,810	8415	9900	0,420	10,40 €
Q2208-ETN9	40	80	23	31,260	9,800	8415	9900	0,510	10,98 €
Q2308-ACC	40	90	33	52,920	15,680	7650	9000	0,930	21,14 €
Q1209-ACC	45	85	19	22,440	7,640	8415	9900	0,470	10,77 €
Q2209-ACC	45	85	23	31,850	10,390	7650	9000	0,550	13,24 €
Q2309-ACC	45	100	36	62,430	18,910	6885	8100	1,250	31,94 €
Q1210-ACC	50	90	20	25,970	8,970	7650	9000	0,530	12,14 €
Q2210-ACC	50	90	23	33,120	10,980	7268	8550	0,600	14,99 €
Q1310-ETN9	50	110	27	42,730	13,720	6120	7200	1,200	25,73 €
Q2310-ACC	50	110	40	62,430	19,600	7268	8550	1,650	39,13 €
Q1211-ETN9	55	100	21	27,050	10,390	6885	8100	0,710	16,18 €
Q2211-ACC	55	100	25	38,220	13,130	6503	7650	0,810	21,05 €
Q1311-ACC	55	120	29	49,690	17,640	5738	6750	1,600	29,49 €
Q2311-ACC	55	120	43	74,580	23,520	5738	6750	2,100	76,04 €
Q1212-ACC	60	110	22	30,580	11,960	6503	7650	0,900	18,48 €
Q2212-ACC	60	110	28	47,820	16,660	6120	7200	1,100	26,46 €
Q1312-ACC	60	130	31	57,330	21,560	4820	5670	1,950	36,19 €
Q2312-ACC	60	130	46	85,360	27,930	5355	6300	2,600	78,30 €
Q1213-ACC	65	120	23	34,400	13,720	5355	6300	1,150	22,12 €
Q2213-ACC	65	120	31	56,060	19,600	5355	6300	1,450	31,97 €
Q2215-ACC	75	130	31	57,330	21,560	4820	5670	1,600	40,51 €
Q2216-ACC	80	140	33	63,700	24,990	4590	5400	2,000	44,43 €
Q2218-ACC	90	160	40	68,800	27,930	4055	4770	3,400	88,40 €

Dimensions in mm

Our other products



FB_ECO

Eco. range steel bevel gear, 4:1



ZG4

Plastic spur gear, Machined plastic (delrin)



PM2

Worm and wheel set, Hardened steel



ASL

45° Hoist ring for welding, for 45° lifts - for welding




BOX-CS

Hose clamp, Box set of steel hose clamps



EPRC

High helix leadscrew, Cylindrical nut - up to 40mm per rotation



JFM

Flanged polymer bush, Universal polymer




RPP

Connecting plate for RPP type timing belts, RPP14



PSG125S

Spur gear - precision range, Stainless steel




PM4

Worm and wheel set, Machined plastic



TBD

Manual leadscrew table with opposing



AC

Strike for toggle latch, 18mm

Complementary products




Q4

Double row radial contact ball bearing, Radial contact - Steel



QTR

Tapered roller bearing, Steel



KM

Bearing locknut, Locknut KM



EAR

Bearing locknut, Self locking locknut - nylon lock washer