

Fixable articulated foot Ø40 and Ø50 **Ste****Sta****Stock**

PR40 PR50

Accepts loads up to 11,000N

- Levelling foot
- Rubber anti-slip sole (NBR 70 Shore)
- Black glass fibre reinforced Polyamide base
- Threaded ball ended spindle in plated steel or stainless steel
- Nut not supplied

With non-slip sole


Steel or stainless steel spindle

Advantages

- Self aligning on floor due to use of ball ended rod
- Flexible and non-slip sole

Info.

- If subjected to vibration, the static loads given will be reduced



DISCOUNTS

Qty	1+	20+	50+
Disc.	List	-10%	On request

Part number	ØD	Thread ØF	B	A	A/F	G	H	H1	Static load (N)	Price each 1 to 19	
Steel spindle											
PR40-6-25	40	M6	25	27	12	16,5	52	55	5000	- 5,25 €	
PR40-6-50	40	M6	50	27	12	16,5	77	80	5000	- 5,25 €	
PR40-8-50	40	M8	50	27	12	16,5	77	80	10000	✓ 5,84 €	
PR40-8-100	40	M8	100	27	12	16,5	127	130	10000	✓ 8,09 €	
PR50-10-75	50	M10	75	30	14	20,0	105	108	11000	✓ 7,88 €	
PR50-10-125	50	M10	125	30	14	20,0	155	158	11000	✓ 9,40 €	
PR50-12-75	50	M12	75	30	14	20,0	105	108	11000	✓ 8,64 €	
PR50-12-125	50	M12	125	30	14	20,0	155	158	11000	✓ 9,65 €	
PR50-16-75	50	M16	75	30	16	20,0	105	108	11000	- 9,75 €	
PR50-16-125	50	M16	125	30	16	20,0	155	158	11000	- 10,92 €	
Stainless steel spindle											
PR40-6-25/SS	40	M6	25	27	12	16,5	52	55	5000	- 7,93 €	
PR40-6-50/SS	40	M6	50	27	12	16,5	77	80	5000	- 10,01 €	
PR40-8-50/SS	40	M8	50	27	12	16,5	77	80	10000	✓ 10,94 €	
PR40-8-100/SS	40	M8	100	27	12	16,5	127	130	10000	✓ 15,60 €	
PR50-10-75/SS	50	M10	75	30	14	20,0	105	108	11000	✓ 14,58 €	
PR50-10-125/SS	50	M10	125	30	14	20,0	155	158	11000	✓ 17,95 €	
PR50-12-75/SS	50	M12	75	30	14	20,0	105	108	11000	✓ 13,43 €	
PR50-12-125/SS	50	M12	125	30	14	20,0	155	158	11000	✓ 16,40 €	
PR50-16-75/SS	50	M16	75	30	16	20,0	105	108	11000	- 14,87 €	
PR50-16-125/SS	50	M16	125	30	16	20,0	155	158	11000	- 17,49 €	

*Depending on availability- Dimensions in mm

Our other products



VDS

Sliding lock adjustment system,
Sliding lock for oblong hole



BH02

Single housed bearing assembly, Bearing secured with circlips



DOMI120

Connecting kits, XZ linking kit



DOMI50

Accessories, Turntable




CQA20

Adjustment slide-system miniature, 20



PGR

Folding revolving handle for handwheel, Folding



RPPM

RPP type belt per metre, RPP14 Steel cored polyurethane



DOMI_MD

Domino rotary table, 40/1



CFF

Female rod ends DIN ISO12240-4, Steel / bronze



INS150

Self tapping insert with collar-coarse thread, With collar-



PO

Pull handle - Multi-sector, Tapped recessed insert



BEK

Bearing housing for miniature ballscrew, Bearing housing

Complementary products



ES

Support base (tripod), Plastic



ES

Bipod support base, Plastic



ES

Simple support base (bipod), Plastic



PR65C

Half-articulated foot Ø 65, Ø 65