

# Fixable articulated foot Ø40 and Ø50 **Ste****Sta****Stock**

## PR40 PR50

Accepts loads up to 11,000N

- Levelling foot
- Rubber anti-slip sole (NBR 70 Shore)
- Black glass fibre reinforced Polyamide base
- Threaded ball ended spindle in plated steel or stainless steel
- Nut not supplied

With non-slip sole


Steel or stainless steel spindle

### Advantages

- Self aligning on floor due to use of ball ended rod
- Flexible and non-slip sole

### Info.

- If subjected to vibration, the static loads given will be reduced



### DISCOUNTS

Qty	1+	20+	50+
Disc.	List	-10%	On request

Part number	ØD	Thread ØF	B	A	A/F	G	H	H1	Static load (N)	Price each 1 to 19	
<b>Steel spindle</b>											
PR40-6-25	40	M6	25	27	12	16,5	52	55	5000	- 5,25 €	
PR40-6-50	40	M6	50	27	12	16,5	77	80	5000	- 5,25 €	
PR40-8-50	40	M8	50	27	12	16,5	77	80	10000	✓ 5,84 €	
PR40-8-100	40	M8	100	27	12	16,5	127	130	10000	✓ 8,09 €	
PR50-10-75	50	M10	75	30	14	20,0	105	108	11000	✓ 7,88 €	
PR50-10-125	50	M10	125	30	14	20,0	155	158	11000	✓ 9,40 €	
PR50-12-75	50	M12	75	30	14	20,0	105	108	11000	✓ 8,64 €	
PR50-12-125	50	M12	125	30	14	20,0	155	158	11000	✓ 9,65 €	
PR50-16-75	50	M16	75	30	16	20,0	105	108	11000	- 9,75 €	
PR50-16-125	50	M16	125	30	16	20,0	155	158	11000	- 10,92 €	
<b>Stainless steel spindle</b>											
PR40-6-25/SS	40	M6	25	27	12	16,5	52	55	5000	- 7,93 €	
PR40-6-50/SS	40	M6	50	27	12	16,5	77	80	5000	- 10,01 €	
PR40-8-50/SS	40	M8	50	27	12	16,5	77	80	10000	✓ 10,94 €	
PR40-8-100/SS	40	M8	100	27	12	16,5	127	130	10000	✓ 15,60 €	
PR50-10-75/SS	50	M10	75	30	14	20,0	105	108	11000	✓ 14,58 €	
PR50-10-125/SS	50	M10	125	30	14	20,0	155	158	11000	✓ 17,95 €	
PR50-12-75/SS	50	M12	75	30	14	20,0	105	108	11000	✓ 13,43 €	
PR50-12-125/SS	50	M12	125	30	14	20,0	155	158	11000	✓ 16,40 €	
PR50-16-75/SS	50	M16	75	30	16	20,0	105	108	11000	- 14,87 €	
PR50-16-125/SS	50	M16	125	30	16	20,0	155	158	11000	- 17,49 €	

\*Depending on availability- Dimensions in mm

## Our other products



PRF-P

Aluminium profile feet support, For feet or casters




PCS6ECO

Chain sprocket - steel, 6mm (DIN 04-1)



DCG

Suction cup, 2.5 bellows, natural rubber



PRF LIS

Door seal for aluminium profile, Black NBR



SEV

Vertical stirrup toggle clamp, Vertical Latch Clamp - stainless steel



SCA\_SS

Stainless steel flat cable clamp, Stainless steel



PTGP

Tensioner pulley, For flat belts



RPCplss

Fixed castor with plate, Stainless steel - Polyamide



PGT

Sliding profile, Sliding panel support



SLB

Indexing plunger, stainless steel



PRF4590

Standard aluminium profile, 45 x 90 mm



CHMBR

Reaction arm, CHM and CHMR gear reducers reaction arm

## Complementary products



VQT

Quarter-turn clamp lock, Plastic or stainless steel button



PR65C

Half-articulated foot  $\varnothing$  65,  $\varnothing$  65