



# Idler sprocket for plate chain

For chain ranges 820 and 815

PR820

- For use with CAP820 and CAP815 plate chains

- Materials:

Reinforced polyamide

Stainless steel screws


- Operating temp.: -10°C to +120°C

- For dimensions and bore tolerances, please refer to technical pages


## Advantage

- Two part design facilitates easy assembly

Easy assembly



Two part design




## DISCOUNTS

|       |      |     |            |
|-------|------|-----|------------|
| Qty   | 1+   | 5+  | 10+        |
| Disc. | List | -5% | On request |

| Part number | No. of teeth | ØDE | ØDP    | Bore ØA | Weight (kg) | Price each 1 to 4 |
|-------------|--------------|-----|--------|---------|-------------|-------------------|
| PR820-21-25 | 21           | 129 | 129,26 | 25      | 0,4         | 30,67 €           |
| PR820-21-30 | 21           | 129 | 129,26 | 30      | 0,4         | 30,67 €           |
| PR820-21-35 | 21           | 129 | 129,26 | 35      | 0,4         | 30,67 €           |
| PR820-21-40 | 21           | 129 | 129,26 | 40      | 0,4         | 30,67 €           |
| PR820-21-45 | 21           | 129 | 129,26 | 45      | 0,4         | 30,67 €           |
| PR820-23-25 | 23           | 141 | 141,22 | 25      | 0,5         | 32,38 €           |
| PR820-23-30 | 23           | 141 | 141,22 | 30      | 0,5         | 32,38 €           |
| PR820-23-35 | 23           | 141 | 141,22 | 35      | 0,5         | 32,38 €           |
| PR820-23-40 | 23           | 141 | 141,22 | 40      | 0,5         | 32,38 €           |
| PR820-23-45 | 23           | 141 | 141,22 | 45      | 0,5         | 32,38 €           |
| PR820-25-25 | 25           | 153 | 153,20 | 25      | 0,5         | 32,71 €           |
| PR820-25-30 | 25           | 153 | 153,20 | 30      | 0,5         | 32,71 €           |
| PR820-25-35 | 25           | 153 | 153,20 | 35      | 0,5         | 32,71 €           |
| PR820-25-40 | 25           | 153 | 153,20 | 40      | 0,5         | 32,71 €           |
| PR820-25-45 | 25           | 153 | 153,20 | 45      | 0,5         | 32,71 €           |

Dimensions in mm

## Our other products



RPP

Connecting plate for RPP type timing belts, RPP8



PTCR

Adjustable furniture foot, square tube



NCT

Square tube connector, Fixed angle



PRF-GPA

Guide for aluminium profile, Parallel rails angle



WJUM10

Drylin® W bearing block, Slide



BWU

Compact precision slide, from 1510 N to 10500 N



BOX-WM

Box set of washer - DIN125, Box set of steel washers



GET-AL

Jaw coupling, economy range, Aluminium



BCTH

Mushroom headed button Hygienic Usit®, With female



SSDB

Stainless steel bevel gear, 2:1



SHO

Parallel axis helical gear, Steel 20NCD2



VQT

Quarter-turn clamp lock, Plastic or stainless steel button

## Complementary products



CAP820

Slim slat top chain acetal, Narrow straight range 820



CAP815

Slim slat top chain stainless steel, Narrow range 815



DBL820

Idler for slat top chain, Ranges 820 and 815



PT820

Drive sprocket for slat top chain, Ranges 820 and 815