


Single row cylinder bearing

QN

Free external flange

- Internal ring has two flanges whereas the external ring has no flange
- The axial displacement of the shaft is contained within the interior of the bearing in both directions.
- Bearings and cylinders are capable of supporting high radial loads and high speeds.
- Static and dynamic loads are radial loads. Max working temperature: 150 °C
- Materials:

Steel rings and balls
Pressed steel cage



DISCOUNTS

Qty	1+	6+	20+	40+	60+
Disc.	List -10%	-15%	-20%	On request	

Part number	Ød	ØD1	B	Load (kN)		Speed (rpm)		Weight (kg)	Price each 1 to 5
				Dynamic (C)	Static (Co)	lubricant	Oil		
QN204-J	20	47	14	25	22	14535	17100	0,110	15,42 €
QN206-J	30	62	16	43	36	10710	12600	0,200	16,70 €
QN306-J	30	72	19	57	47	9180	10800	0,360	19,06 €
QN207-J	35	72	17	55	47	9180	10800	0,300	17,52 €
QN307-J	35	80	21	74	62	8415	9900	0,480	25,60 €
QN208-J	40	80	18	61	52	8415	9900	0,370	20,83 €
QN308-J	40	90	23	91	76	7268	8550	0,640	33,67 €
QN309-J	45	100	25	110	98	6503	7650	0,880	38,65 €
QN210-J	50	90	20	72	68	6885	8100	0,480	27,76 €
QN310-J	50	110	27	124	110	6120	7200	1,150	56,13 €
QN211-J	55	100	21	95	93	6120	7200	0,660	33,67 €
QN311-J	55	120	29	153	140	5355	6300	1,450	58,92 €
QN212-J	60	110	22	106	100	5738	6750	0,810	47,76 €
QN312-J	60	130	31	170	157	5126	6030	1,800	61,86 €
QN213-J	65	120	23	120	116	5126	6030	1,050	48,90 €
QN313-J	65	140	33	208	192	4590	5400	2,250	70,77 €
QN214-J	70	125	24	134	134	4820	5670	1,150	50,68 €
QN314-J	70	150	35	231	223	4284	5040	2,750	113,89 €

Dimensions in mm

Our other products



BOXdh

Boxed set of cylindrical dowel pins DIN6325, Boxed set - Solid DIN 6...



BZY_SS

Stainless steel cylindrical elasto mount, Stainless steel



MCL

Cylindrical threaded sleeve, Cylindrical - steel



KKP-AR

Linear bearing with inclined ball tracks, Heavy loads / -20° +200°



PLM-20SC

Cylindrical magnet, Cylindrical magnet



PSG05S

Spur gear - precision range, Stainless steel 316



PTKss

Foot for the food industry, Stainless steel - 3-A standard



M0

Worm and wheel set, Bronze



PR125rehausse

Extension for articulated foot Ø123,



T2

T type timing belt, T2.5 Steel cored



CHMR90

Worm and wheel gear reducer, up to 540



KH

Linear bearing, Light

Complementary products




Q1

Self-aligning radial ball bearing, Steel



NKX

Combined bearing without inner ring, Needle and ball bearings



KM

Bearing locknut, Locknut KM



EAR

Bearing locknut, Self locking locknut - nylon lock washer