



# Idler sprocket for plate chain

For chain ranges 820 and 815

PR820

- For use with CAP820 and CAP815 plate chains

- Materials:

Reinforced polyamide

Stainless steel screws


- Operating temp.: -10°C to +120°C

- For dimensions and bore tolerances, please refer to technical pages


## Advantage

- Two part design facilitates easy assembly

Easy assembly



Two part design



## DISCOUNTS

Qty	1+	5+	10+
Disc.	List	-5%	On request

Part number	No. of teeth	ØDE	ØDP	Bore ØA	Weight (kg)	Price each 1 to 4
PR820-21-25	21	129	129,26	25	0,4	30,67 €
PR820-21-30	21	129	129,26	30	0,4	30,67 €
PR820-21-35	21	129	129,26	35	0,4	30,67 €
PR820-21-40	21	129	129,26	40	0,4	30,67 €
PR820-21-45	21	129	129,26	45	0,4	30,67 €
PR820-23-25	23	141	141,22	25	0,5	32,38 €
PR820-23-30	23	141	141,22	30	0,5	32,38 €
PR820-23-35	23	141	141,22	35	0,5	32,38 €
PR820-23-40	23	141	141,22	40	0,5	32,38 €
PR820-23-45	23	141	141,22	45	0,5	32,38 €
PR820-25-25	25	153	153,20	25	0,5	32,71 €
PR820-25-30	25	153	153,20	30	0,5	32,71 €
PR820-25-35	25	153	153,20	35	0,5	32,71 €
PR820-25-40	25	153	153,20	40	0,5	32,71 €
PR820-25-45	25	153	153,20	45	0,5	32,71 €

Dimensions in mm


## Our other products



F7-SN  
Multifunction display,  
Articulated support



ES  
Support base (tripod),  
Plastic



T0  
Torsion spring,  
Stainless steel




HTD5M-BAR  
HTD type tooth bar  
stock, HTD5




CHML50  
Worm and wheel gear  
reducer, up to 107  
Nm - Integrated  
torque limiter



PRF\_ER  
Joining bar for  
aluminium profile,  
Joint bar



M0  
Worm and wheel set,  
Machined plastic  
(delrin)



G1  
Steel spur gear, Steel  
20NCD2



GB-RA  
Brass spur gear, Brass  
CuZn39Pb3



SEV  
Vertical stirrup toggle  
clamp, Vertical Latch  
Clamp - stainless steel



WJUM20  
Drylin® W bearing  
block, Slide



CHML63  
Worm and wheel gear  
reducer, up to 138  
Nm - Integrated  
torque limiter

## Complementary products



CAP820  
Slim slat top chain  
acetal, Narrow  
straight range 820



CAP815  
Slim slat top chain  
stainless steel,  
Narrow range 815



DBL820  
Idler for slat top  
chain, Ranges 820  
and 815



PT820  
Drive sprocket for slat  
top chain, Ranges 820  
and 815