



# Idler sprocket for plate chain

For chain ranges 820 and 815

PR820

- For use with CAP820 and CAP815 plate chains

- Materials:

Reinforced polyamide

Stainless steel screws


- Operating temp.: -10°C to +120°C

- For dimensions and bore tolerances, please refer to technical pages


## Advantage

- Two part design facilitates easy assembly

Easy assembly



Two part design



## DISCOUNTS

Qty	1+	5+	10+
Disc.	List	-5%	On request

Part number	No. of teeth	ØDE	ØDP	Bore ØA	Weight (kg)	Price each 1 to 4
PR820-21-25	21	129	129,26	25	0,4	30,67 €
PR820-21-30	21	129	129,26	30	0,4	30,67 €
PR820-21-35	21	129	129,26	35	0,4	30,67 €
PR820-21-40	21	129	129,26	40	0,4	30,67 €
PR820-21-45	21	129	129,26	45	0,4	30,67 €
PR820-23-25	23	141	141,22	25	0,5	32,38 €
PR820-23-30	23	141	141,22	30	0,5	32,38 €
PR820-23-35	23	141	141,22	35	0,5	32,38 €
PR820-23-40	23	141	141,22	40	0,5	32,38 €
PR820-23-45	23	141	141,22	45	0,5	32,38 €
PR820-25-25	25	153	153,20	25	0,5	32,71 €
PR820-25-30	25	153	153,20	30	0,5	32,71 €
PR820-25-35	25	153	153,20	35	0,5	32,71 €
PR820-25-40	25	153	153,20	40	0,5	32,71 €
PR820-25-45	25	153	153,20	45	0,5	32,71 €

Dimensions in mm

## Our other products



CHTRP

Single and dual output gearboxes, Up to 87,3Nm



VTAP

Magnetic head screw, With rubber coating



MAX22

Motor-gearbox 12V and 24V DC, from 0,07 to 0,2Nm



SBS\_M

Single chain supplied by the metre, Stainless steel



BAC105

Storage bin, 8mm




AT10courroie

AT type timing belt, AT10 Steel cored polyurethane



PRES2HR

Manual workbench press, Force up to 200kg



PRF\_PSA

Shaft support for aluminium profile, Shaft support




NSO

Housing for open linear bearing, Opened - long



PGR

Folding revolving handle for handwheel, Folding



PM3

Worm and wheel set, Machined plastic (delrin)



SA\_SAKH

Housing for linear bearing, Closed - light load

## Complementary products



CAP820

Slim slat top chain acetal, Narrow straight range 820



CAP815

Slim slat top chain stainless steel, Narrow range 815



DBL820

Idler for slat top chain, Ranges 820 and 815



PT820

Drive sprocket for slat top chain, Ranges 820 and 815