

- **Levelling foot**
- Non slip base
- Materials:
 - Base: Black glass reinforced polyamide (Shore 70)
 - Spindle: Zinc plated steel or stainless 304 steel
- Supplied without nut




Advantages

- Articulated rod allows auto-alignment with the ground
- Sole material ensures flexibility and grip

Info.

- Values given for static, should will be reduced in case of a vibrating load

With non-slip base



DISCOUNTS

Qty	1+	20+	50+
Disc.	List -10%	On request	

Part number	ØD	Thread		B	A	A/F	G	H	H1	Static load (N)	Type	Price each
		ØF	B									
Steel spindle												
PR85-12-75	83	M12	75	38	14	27	113	116	15000	H	✓	10,59 €
PR85-12-125	83	M12	125	38	14	27	163	166	15000	H	✓	11,83 €
PR85-16-75	83	M16	75	38	16	27	113	116	20000	H	✓	11,14 €
PR85-16-150	83	M16	150	38	16	27	188	191	20000	H	✓	13,10 €
PR85-16-200	83	M16	200	38	16	27	238	241	20000	H	✓	14,43 €
PR85-20-125	83	M20	125	41	17	27	166	169	20000	M	✓	12,13 €
PR85-20-175	83	M20	175	41	17	27	216	219	20000	M	✓	13,86 €
PR85-20-225	83	M20	225	41	17	27	266	269	20000	M	✓	15,75 €
Stainless steel spindle												
PR85-12-75/SS	83	M12	75	38	14	27	113	116	15000	H	✓	17,99 €
PR85-12-125/SS	83	M12	125	38	14	27	163	166	15000	H	✓	20,70 €
PR85-16-75/SS	83	M16	75	41	13	27	116	119	20000	M	✓	17,99 €
PR85-16-150/SS	83	M16	150	41	13	27	191	194	20000	M	✓	22,05 €
PR85-16-200/SS	83	M16	200	41	13	27	241	244	20000	M	✓	24,79 €
PR85-20-125/SS	83	M20	125	41	17	27	166	169	20000	M	✓	25,21 €
PR85-20-175/SS	83	M20	175	41	17	27	216	219	20000	M	✓	29,70 €
PR85-20-225/SS	83	M20	225	41	17	27	266	269	20000	M	✓	35,90 €

*Depending on availability - Dimensions in mm

Our other products



GAC
Latch clamp with lock,
Lockable



RLX
Free running conveyor
roller, PVC



TCL-ECL
Support rod for heavy
loads, Support spindle



HTD5M_09
HTD Heavy duty
timing pulley, HTD5
Aluminium



BAG-MISS
Split shaft collar with
clamp lever, Stainless
steel



H1
Crossed helical gear
crossed axis at 90°,
Steel 20NCD2



PR125rehausse
Extension for
articulated foot Ø123,
articulated foot PR125



PRF_PGN
Door handle for
aluminium profile,
Handle with lock
suitable



PNA
PERIFLEX® elastic
coupling, Complete
coupling



P45
Worm and wheel gear
reducer, up to 40 Nm



KB_WW
Closed linear
precision bearing,
Economy range



PLM-SC
Magnetic stud with
threaded hole, With
threaded hole

Complementary products



PR65C
Half-articulated foot Ø
65, Ø 65



ES
Support base (tripod),
Plastic



ES
Bipod support base,
Plastic



ES
Simple support base
(bipod), Plastic