

- **Levelling foot**
- Non slip base
- Materials:
  - Base: Black glass reinforced polyamide (Shore 70)
  - Spindle: Zinc plated steel or stainless 304 steel
- Supplied without nut




### Advantages

- Articulated rod allows auto-alignment with the ground
- Sole material ensures flexibility and grip

### Info.

- Values given for static, should will be reduced in case of a vibrating load

**With non-slip base**



### DISCOUNTS

Qty	1+	20+	50+
Disc.	List -10%	On request	

Part number	ØD	Thread		B	A	A/F	G	H	H1	Static load (N)	Type	Price each
		ØF	B									
<b>Steel spindle</b>												
PR85-12-75	83	M12	75	38	14	27	113	116	15000	H	✓	10,59 €
PR85-12-125	83	M12	125	38	14	27	163	166	15000	H	✓	11,83 €
PR85-16-75	83	M16	75	38	16	27	113	116	20000	H	✓	11,14 €
PR85-16-150	83	M16	150	38	16	27	188	191	20000	H	✓	13,10 €
PR85-16-200	83	M16	200	38	16	27	238	241	20000	H	✓	14,43 €
PR85-20-125	83	M20	125	41	17	27	166	169	20000	M	✓	12,13 €
PR85-20-175	83	M20	175	41	17	27	216	219	20000	M	✓	13,86 €
PR85-20-225	83	M20	225	41	17	27	266	269	20000	M	✓	15,75 €
<b>Stainless steel spindle</b>												
PR85-12-75/SS	83	M12	75	38	14	27	113	116	15000	H	✓	17,99 €
PR85-12-125/SS	83	M12	125	38	14	27	163	166	15000	H	✓	20,70 €
PR85-16-75/SS	83	M16	75	41	13	27	116	119	20000	M	✓	17,99 €
PR85-16-150/SS	83	M16	150	41	13	27	191	194	20000	M	✓	22,05 €
PR85-16-200/SS	83	M16	200	41	13	27	241	244	20000	M	✓	24,79 €
PR85-20-125/SS	83	M20	125	41	17	27	166	169	20000	M	✓	25,21 €
PR85-20-175/SS	83	M20	175	41	17	27	216	219	20000	M	✓	29,70 €
PR85-20-225/SS	83	M20	225	41	17	27	266	269	20000	M	✓	35,90 €

\*Depending on availability - Dimensions in mm

## Our other products



GP75

Spring loaded toggle latch, Standard (GP75)




SH2

Parallel axis helical gear, Machined plastic (delrin)



BLHT70

Right angled gearbox, from 26 to 128 Nm



M1

Worm and wheel set, Bronze



SH0

Parallel axis helical gear, Machined plastic (delrin)



BIMSS

Indexing plunger mini, miniature - Stainless steel



PM2

Worm and wheel set, Machined plastic (delrin)



NT63

Spur gear coaxial gearbox, from 8 to 20 Nm - In-line



SH1

Parallel axis helical gear, Machined plastic (delrin)



MEP

Revolving handle for handwheel, Fixed



PSG3

Spur gear - precision range, Pre-hardened Steel 35NCD6



RFK48B

Hypoid gearbox - Stainless steel, up to 350 Nm

## Complementary products



PR65C

Half-articulated foot Ø 65, Ø 65



ES

Support base (tripod), Plastic



ES

Bipod support base, Plastic



ES

Simple support base (bipod), Plastic