


Single row cylindrical roller bearings

QNUP

One fixed internal flange and one free internal flange

- The external ring has two fixed flanges whereas the internal ring has one fixed and one free flange.
- The axial movement of the shaft is restricted in both directions.
- Static and dynamic loads are radial loads
- Max working temperature: Polyamide cage: 120°C
Steel or brass cage: 150°C
- Materials:
 - Steel flanges and cylinders
 - P: polyamide cage
 - M: solid brass cage
 - J: pressed steel cage



DISCOUNTS

Qty	1+	6+	20+	40+	60+
Disc.	List -10%	-15%	-20%	On request	

Part number	Ød	ØD1	B	Load (kN)		Speed (rpm)		Weight (kg)	Price each 1 to 5
				Dynamic (C)	Static (Co)	lubricant Grease	Oil		
QNUP203-M	17	40	12	17	14	16830	19800	0,073	15.15 €
QNUP2203-P	17	40	16	23	21	16830	19800	0,097	25.36 €
QNUP204-P	20	47	14	25	22	14535	17100	0,12	15.87 €
QNUP205-J	25	52	15	28	26	12240	14400	0,14	17.68 €
QNUP2205-M	25	52	18	33	33	12240	14400	0,17	26.94 €
QNUP206-P	30	62	16	43	36	10710	12600	0,22	21.75 €
QNUP2206-J	30	62	20	54	48	10710	12600	0,27	29.34 €
QNUP207-J	35	72	17	55	47	9180	10800	0,32	23.10 €
QNUP2207-P	35	72	23	68	62	9180	10800	0,42	30.78 €
QNUP307-J	35	80	21	74	62	8415	9900	0,51	29.08 €
QNUP2307-J	35	80	31	104	96	8415	9900	0,75	44.20 €
QNUP208-J	40	80	18	61	52	8415	9900	0,4	29.73 €
QNUP2308-J	40	90	33	126	118	7268	8550	0,98	53.86 €
QNUP209-J	45	85	19	68	63	7268	8550	0,45	31.11 €
QNUP210-P	50	90	20	72	68	6885	8100	0,51	31.80 €
QNUP2310-J	50	110	40	182	182	6120	7200	1,8	75.16 €
QNUP211-J	55	100	21	95	93	6120	7200	0,69	35.37 €
QNUP311-P	55	120	29	153	140	5355	6300	1,55	54.55 €
QNUP212-J	60	110	22	106	100	5738	6750	0,86	41.62 €
QNUP213-M	65	120	23	120	116	5126	6030	1,1	47.86 €

Dimensions in mm

Our other products



GMK17_R
Round guide, Round
guide for conical
profile



DOMI30
Connecting kits, XY
linking kit



PCS37K
Chain sprocket with
hardened teeth,
9.525mm (DIN06B-1)



SSG1
Stainless steel spur
gear, Stainless steel
304L



CTss
Universal joint,
telescopic, Inox, Light
duty




CHMR40
Worm and wheel gear
reducer, up to 57 Nm



DBL880
Idler for slat top
chain, Ranges 880
and 881



MEP
Revolving handle for
handwheel, Fixed



LAT1
1A motorised linear
actuator, 1 ampere



CDR
Retaining cable for
ball pin, Retaining



SERB
Cam latch, Cam latch



INO
Internal gear, Steel
20NCD2


Complementary products



Q1
Self-aligning radial
ball bearing, Steel



NKX
Combined bearing
without inner ring,
Needle and ball
bearings



KM
Bearing locknut,
Locknut KM



EAR
Bearing locknut, Self
locking locknut - nylon
lock washer