

- **Levelling foot**
- Non slip base
- Materials:
 - Base: Black glass reinforced polyamide (Shore 70)
 - Spindle: Zinc plated steel or stainless 304 steel
- Supplied without nut



Advantages

- Articulated rod allows auto-alignment with the ground
- Sole material ensures flexibility and grip

Info.

- Values given for static, should will be reduced in case of a vibrating load

With non-slip base



Hexagonal

Flat

DISCOUNTS

Qty	1+	20+	50+
Disc.	List -10%	On request	

Part number	ØD	Thread		B	A	A/F	G	H	H1	Static load (N)	Type	Price each
		ØF	B									
Steel spindle												
PR85-12-75	83	M12	75	38	14	27	113	116	15000	H	✓	10,59 €
PR85-12-125	83	M12	125	38	14	27	163	166	15000	H	✓	11,83 €
PR85-16-75	83	M16	75	38	16	27	113	116	20000	H	✓	11,14 €
PR85-16-150	83	M16	150	38	16	27	188	191	20000	H	✓	13,10 €
PR85-16-200	83	M16	200	38	16	27	238	241	20000	H	✓	14,43 €
PR85-20-125	83	M20	125	41	17	27	166	169	20000	M	✓	12,13 €
PR85-20-175	83	M20	175	41	17	27	216	219	20000	M	✓	13,86 €
PR85-20-225	83	M20	225	41	17	27	266	269	20000	M	✓	15,75 €
Stainless steel spindle												
PR85-12-75/SS	83	M12	75	38	14	27	113	116	15000	H	✓	17,99 €
PR85-12-125/SS	83	M12	125	38	14	27	163	166	15000	H	✓	20,70 €
PR85-16-75/SS	83	M16	75	41	13	27	116	119	20000	M	✓	17,99 €
PR85-16-150/SS	83	M16	150	41	13	27	191	194	20000	M	✓	22,05 €
PR85-16-200/SS	83	M16	200	41	13	27	241	244	20000	M	✓	24,79 €
PR85-20-125/SS	83	M20	125	41	17	27	166	169	20000	M	✓	25,21 €
PR85-20-175/SS	83	M20	175	41	17	27	216	219	20000	M	✓	29,70 €
PR85-20-225/SS	83	M20	225	41	17	27	266	269	20000	M	✓	35,90 €

*Depending on availability - Dimensions in mm

Our other products



RFK28C
Hypoid gearbox -
Stainless steel, up to
130 Nm



SUPTOOL
Installation tools for
clamping hub, For
hexagonal clamping
hub



SLB
Indexing plunger,
steel class 5.8



PFM
Fixed levelling foot,
Flanged plate



BCAss
Stainless steel splined
bush, Inox



PM2
Worm and wheel set,
Non hardened steel



NT62
Spur gear coaxial
gearbox, from 6 to 18
Nm - Inline



NT61
Spur gear coaxial
gearbox, from 5 to 14
Nm - Inline



GMK17_BR
Clamp for guiding
profile, Rounded only
- single



RBGpl
Swivel castor with
double brake, Steel -
grey rubber



PM2
Worm and wheel set,
Machined plastic
(delrin)



ACLALF
Adjustable foot for
aluminium profile,
Ideal for workstations

Complementary products



PR65C
Half-articulated foot Ø
65, Ø 65



ES
Support base (tripod),
Plastic



ES
Bipod support base,
Plastic



ES
Simple support base
(bipod), Plastic