

Die spring ISO 10243




R **Blue: medium duty**

- ISO blue standard (ISO 10243)
- Extra-rigid spring
- For medium loads
- Trapezoidal wire
- Ends squared and ground
- Withstands shocks
- Tolerates shaking
- Easy to compress to solid height
- Material: chromium-vanadium steel



Advantages

- The trapezoidal wire permits optimum deflection whilst protecting against the risk of damage caused by overloading the spring.
- Hardness sufficient to allow heavy loads to be withstood.
- Heat resistant up to 230°C.
- Uniform spring performance.
- Uniform stiffness ratio
- Greater load accuracy for a given height.
- Reliable performance.
- Reduced risk of breakage.



Option

- Other sizes



DISCOUNTS

Qty	1+	6+	10+	20+	40+
Disc.	List	-15%	-20%	-25%	On request

Part number	Hole ØA (mm)	Rod ØB (mm)	Free length Lo (mm)	Load at 1 mm deflection (N)	Load table								Price each 1 to 5
					Optimum life (25% free length Lo)		Long life (30% free length Lo)		Max. working (35% free length Lo)		Max. deflection		
					Load (N)	Deflection (mm)	Load (N)	Deflection (mm)	Load (N)	Deflection (mm)	Load (N)	Deflection (mm)	
R204104	10,0	5,0	25	16,0	80,0	5,0	100,0	6,3	120,0	7,5	152,0	9,5	2,00 €
R204106	10,0	5,0	38	11,9	90,4	7,6	113,1	9,5	135,7	11,4	171,4	14,4	2,30 €
R204108	10,0	5,0	51	8,9	90,8	10,2	113,5	12,8	136,2	15,3	172,7	19,4	3,21 €
R204112	10,0	5,0	76	5,3	80,6	15,2	100,7	19,0	120,8	22,8	153,2	28,9	3,98 €
R204204	12,5	6,3	25	30,0	150,0	5,0	187,5	6,3	225,0	7,5	285,0	9,5	2,99 €
R204206	12,5	6,3	38	21,4	162,6	7,6	203,3	9,5	244,0	11,4	308,2	14,4	3,54 €
R204208	12,5	6,3	51	15,5	158,1	10,2	197,6	12,8	237,2	15,3	300,7	19,4	4,06 €
R204212	12,5	6,3	76	10,2	155,0	15,2	193,8	19,0	232,6	22,8	294,8	28,9	5,27 €
R204248	12,5	6,3	305	2,1	128,1	61,0	160,1	76,3	192,2	91,5	243,6	116,0	16,95 €
R204304	16,0	8,0	25	49,4	247,0	5,0	308,8	6,3	370,5	7,5	469,3	9,5	3,85 €
R204306	16,0	8,0	38	33,9	257,6	7,6	322,1	9,5	386,5	11,4	488,2	14,4	3,98 €
R204308	16,0	8,0	51	26,4	269,3	10,2	336,6	12,8	403,9	15,3	512,2	19,4	4,84 €
R204312	16,0	8,0	76	17,8	270,6	15,2	338,2	19,0	405,8	22,8	514,4	28,9	5,31 €
R204316	16,0	8,0	102	13,5	275,4	20,4	344,3	25,5	413,1	30,6	523,8	38,8	6,26 €
R204404	20,0	10,0	25	98,0	490,0	5,0	612,5	6,3	735,0	7,5	921,2	9,4	4,02 €
R204406	20,0	10,0	38	56,0	425,6	7,6	532,0	9,5	638,4	11,4	784,0	14,0	4,29 €

Dimensions in mm

Part number	Hole ØA (mm)	Rod ØB (mm)	Free length Lo (mm)	Load at 1 mm deflection (N)	Load table								Price each 1 to 5
					Optimum life (25% free length Lo)		Long life (30% free length Lo)		Max. working (35% free length Lo)		Max. deflection		
					Load (N)	Deflection (mm)	Load (N)	Deflection (mm)	Load (N)	Deflection (mm)	Load (N)	Deflection (mm)	
R204408	20,0	10,0	51	41,7	425,3	10,2	531,7	12,8	638,0	15,3	792,3	19,0	4,84 €
R204412	20,0	10,0	76	25,1	381,5	15,2	476,9	19,0	572,3	22,8	702,8	28,0	5,91 €
R204416	20,0	10,0	102	19,8	403,9	20,4	504,9	25,5	605,9	30,6	752,4	38,0	8,01 €
R204420	20,0	10,0	127	16,6	421,6	25,4	527,1	31,8	632,5	38,1	796,8	48,0	9,82 €
R204424	20,0	10,0	152	13,2	401,3	30,4	501,6	38,0	601,9	45,6	752,4	57,0	10,43 €
R204504	25,0	12,5	25	147,0	735,0	5,0	918,8	6,3	1102,5	7,5	1381,8	9,4	3,98 €
R204506	25,0	12,5	38	93,0	706,8	7,6	883,5	9,5	1060,2	11,4	1302,0	14,0	4,96 €
R204507	25,0	12,5	44	80,8	711,0	8,8	888,8	11,0	1066,6	13,2	1333,2	16,5	6,13 €
R204508	25,0	12,5	51	68,6	699,7	10,2	874,7	12,8	1049,6	15,3	1303,4	19,0	6,65 €
R204510	25,0	12,5	64	53,0	678,4	12,8	848,0	16,0	1017,6	19,2	1272,0	24,0	7,54 €
R204512	25,0	12,5	76	43,2	656,6	15,2	820,8	19,0	985,0	22,8	1209,6	28,0	8,28 €
R204514	25,0	12,5	89	38,2	680,0	17,8	850,0	22,3	1019,9	26,7	1260,6	33,0	9,82 €
R204516	25,0	12,5	102	33,0	673,2	20,4	841,5	25,5	1009,8	30,6	1254,0	38,0	10,90 €
R204518	25,0	12,5	115	28,0	644,0	23,0	805,0	28,8	966,0	34,5	1204,0	43,0	11,11 €
R204520	25,0	12,5	127	25,9	657,9	25,4	822,3	31,8	986,8	38,1	1243,2	48,0	12,01 €
R204522	25,0	12,5	139	23,2	645,0	27,8	806,2	34,8	967,4	41,7	1206,4	52,0	13,35 €
R204524	25,0	12,5	152	20,8	632,3	30,4	790,4	38,0	948,5	45,6	1185,6	57,0	14,15 €
R204528	25,0	12,5	178	17,8	633,7	35,6	792,1	44,5	950,5	53,4	1192,6	67,0	15,45 €
R204532	25,0	12,5	203	15,8	641,5	40,6	801,9	50,8	962,2	60,9	1200,8	76,0	17,17 €
R204548	25,0	12,5	305	10,2	622,2	61,0	777,8	76,3	933,3	91,5	1162,8	114,0	41,95 €
R204606	32,0	16,0	38	185,0	1406,0	7,6	1757,5	9,5	2109,0	11,4	2590,0	14,0	7,17 €
R204607	32,0	16,0	44	158,0	1390,4	8,8	1738,0	11,0	2085,6	13,2	2607,0	16,5	8,01 €
R204608	32,0	16,0	51	134,0	1366,8	10,2	1708,5	12,8	2050,2	15,3	2546,0	19,0	8,71 €
R204610	32,0	16,0	64	99,0	1267,2	12,8	1584,0	16,0	1900,8	19,2	2376,0	24,0	9,82 €
R204612	32,0	16,0	76	80,5	1223,6	15,2	1529,5	19,0	1835,4	22,8	2254,0	28,0	10,67 €
R204616	32,0	16,0	102	58,8	1199,5	20,4	1499,4	25,5	1799,3	30,6	2234,4	38,0	13,78 €
R204620	32,0	16,0	127	44,8	1137,9	25,4	1422,4	31,8	1706,9	38,1	2150,4	48,0	18,37 €
R204624	32,0	16,0	152	37,8	1149,1	30,4	1436,4	38,0	1723,7	45,6	2154,6	57,0	18,88 €
R204632	32,0	16,0	203	28,9	1173,3	40,6	1466,7	50,8	1760,0	60,9	2196,4	76,0	23,52 €
R204648	32,0	16,0	305	18,3	1116,3	61,0	1395,4	76,3	1674,5	91,5	2086,2	114,0	42,94 €
R204708	40,0	20,0	51	181,6	1852,3	10,2	2315,4	12,8	2778,5	15,3	3450,4	19,0	10,25 €
R204712	40,0	20,0	76	108,0	1641,6	15,2	2052,0	19,0	2462,4	22,8	3024,0	28,0	13,60 €
R204716	40,0	20,0	102	81,0	1652,4	20,4	2065,5	25,5	2478,6	30,6	3078,0	38,0	19,10 €
R204720	40,0	20,0	127	62,7	1592,6	25,4	1990,7	31,8	2388,9	38,1	3009,6	48,0	24,25 €
R204724	40,0	20,0	152	51,6	1568,6	30,4	1960,8	38,0	2353,0	45,6	2941,2	57,0	24,85 €
R204732	40,0	20,0	203	36,7	1490,0	40,6	1862,5	50,8	2235,0	60,9	2789,2	76,0	34,30 €
R204748	40,0	20,0	305	24,6	1500,6	61,0	1875,8	76,3	2250,9	91,5	2804,4	114,0	51,66 €
R204810	50,0	25,0	64	209,0	2675,2	12,8	3344,0	16,0	4012,8	19,2	5016,0	24,0	19,82 €
R204814	50,0	25,0	89	140,0	2492,0	17,8	3115,0	22,3	3738,0	26,7	4620,0	33,0	23,35 €
R204818	50,0	25,0	115	106,0	2438,0	23,0	3047,5	28,8	3657,0	34,5	4558,0	43,0	29,41 €
R204822	50,0	25,0	139	87,0	2418,6	27,8	3023,3	34,8	3627,9	41,7	4524,0	52,0	35,08 €
R204828	50,0	25,0	178	69,5	2474,2	35,6	3092,8	44,5	3711,3	53,4	4656,5	67,0	42,42 €
R204836	50,0	25,0	229	50,9	2331,2	45,8	2914,0	57,3	3496,8	68,7	4377,4	86,0	57,67 €
R204848	50,0	25,0	305	38,6	2354,6	61,0	2943,3	76,3	3531,9	91,5	4400,4	114,0	90,27 €
R204912	63,0	38,0	76	312,0	4742,4	15,2	5928,0	19,0	7113,6	22,8	8736,0	28,0	47,31 €
R204916	63,0	38,0	102	221,0	4508,4	20,4	5635,5	25,5	6762,6	30,6	8398,0	38,0	57,41 €
R204920	63,0	38,0	127	168,0	4267,2	25,4	5334,0	31,8	6400,8	38,1	8064,0	48,0	58,18 €
R204928	63,0	38,0	178	114,0	4058,4	35,6	5073,0	44,4	6087,6	53,4	7638,0	67,0	87,04 €
R204936	63,0	38,0	229	89,2	4085,4	45,8	5106,7	57,3	6128,0	68,7	7671,2	86,0	98,68 €
R204948	63,0	38,0	305	64,7	3946,7	61,0	4933,4	76,3	5920,1	91,5	7375,8	114,0	137,25 €

Dimensions in mm

Our other products



VB

Small 6 lobe threaded handle - female, Duroplast - Stainless steel



CCLSS

Stainless steel wire thimble, Stainless steel



CABtool

Fitting cable tools, Crimping tools



PCS50

Chain sprocket - steel, 12.7mm (DIN08B-1)



PFL

P-FLEX Coupling, Set screw



SHA_PTR

Handwheel with folding handle, Polyamide



GAL_25

Ø25 conveyor roller, Without ball bearing



TBE16

Economic mini-table with trapezoidal leadscrew, 5kg




TSRTC

Stem support for caster, For swivel caster with central



TBbutee

Axial thrust bearing, Steel balls



RPPM

RPP type belt per metre, RPP5 Steel cored polyurethane



ADSR

Backlash free coupling Gerwah®, from 12.5 to 525Nm

Complementary products



R205

Die spring ISO10243, Heavy



R206

Die spring ISO10243, Extra-heavy



CDGamme

Compression spring DIN2095, DIN 2095



CDC

Conical compression spring, Conical