

# Manual workbench press



## PRES2HR

## Force up to 200 kg


- Rack press
- The force is linear and constant over the full stroke.
- The ram is prevented from turning
- Free height is adjustable
- Stroke adjusts via a screw
- Quick and easy to install

### Applications

- This model is particularly robust and is frequently used for the assembly of parts, simple bending tasks and various fastening operations

### Option

- None available



### DISCOUNTS

Qty	1+	2+
Disc.	List	On request

Part number	Force (kg)	Free height HL (mm)	Stroke (mm)	Goose neck depth (mm)	Weight (kg)	Stock*	Price each
PRES-2HR	200	54 - 200	50	72	8	✓	672,26 €

\*Depending on availability - Dimensions in mm



# Manual workbench press

Force up to **400 kg**

**PRES3HR**

- Rack press
- The force is linear and constant over the full stroke.
- The ram is prevented from turning
- Free height is adjustable
- Stroke adjusts via a screw
- Quick and easy to install

## Applications


- This model is particularly robust and is frequently used for the assembly of parts, simple bending tasks and various fastening operations

## Options

- 5 digit counter with reset button
- Accessories- see accessory page (tome 5 p.21)



version with counter



## DISCOUNTS

Qty	1+	2+
Disc.	List	On request

Part number	Force (kg)	Free height HL (mm)	Stroke (mm)	Goose neck depth (mm)	Weight (kg)	Counter	Stock*	Price each
PRES-3HR	400	35 - 270	80	80	17	Without	✓	1 069,70 €
PRES-3HR-CPT	400	35 - 270	80	80	17	With	-	1 454,33 €

\*Depending on availability - Dimensions in mm

# Manual workbench press



## PRES4HR

## Force up to 600 kg

- Rack press
- The force is linear and constant over the full stroke.
- The ram is prevented from turning
- Free height is adjustable
- Stroke adjusts via a screw
- Quick and easy to install

### Applications


- This model is particularly robust and is frequently used for the assembly of parts, simple bending tasks and various fastening operations

### Options

- 5 digit counter with reset button
- Accessories- see accessory page (tome 5 p.21)



version with counter



### DISCOUNTS

Qty	1+	2+
Disc.	List	On request

Part number	Power (kg)	Free height HL (mm)	Stroke (mm)	Goose neck depth (mm)	Weight (kg)	Counter	Price each
PRES-4HR	600	46 - 280	100	95	25	Without	1 189,91 €
PRES-4HR-CPT	600	46 - 280	100	95	25	With	1 574,51 €

Dimensions in mm



# Manual bench press


**500 kg** capacity

**PRES5HR**

- **Knee-joint press**
- The maximum power is reached at the end of the stroke
- The travelling nut is prevented from turning
- Adjustable free height
- Screw stroke adjustment
- Quick and easy installation

## Uses

- This model is particularly robust and is normally used for the assembly of parts, simple bending tasks and various fastening operations



## DISCOUNTS

Qty	1+	2+
Disc.	List	On request

Part number	Power (kg)	Free height HL (mm)	Stroke length (mm)	Goose neck depth (mm)	Weight (kg)	Stock*	Price each
PRES-5HR	500	42 - 185	50	72	9	✓	605.97 €

\*Depending on availability - Dimensions in mm

# Manual bench press




## PRES7HR

## 700 kg capacity

- **Knee-joint press**
- The maximum power is reached at the end of the stroke
- The travelling nut is prevented from turning
- Adjustable free height
- Screw stroke adjustment
- Quick and easy installation

### Uses

- This model is particularly robust and is normally used for the assembly of parts, simple bending tasks and various fastening operations



### DISCOUNTS

Qty	1+	2+
Disc.	List	On request

Part number	Power (kg)	Free height HL (mm)	Stroke length (mm)	Goose neck depth (mm)	Weight (kg)	Price each
PRES-7HR	700	35 - 260	40	95	25	1 244,00 €

Dimensions in mm

# Manual workbench press

## Accessories for PRES-3HR and PRES-4HR presses

# PRES

These accessories are only suitable for use with the PRES-3HR and PRES-4HR presses

**PRES-PMB:** Micrometric adjustment PMB.  
Bottom dead centre adjustment system, graduated every 0.02 mm

**PRES-TE:** Slot nuts for securing tools in the T slot

**PRES-ER25:** Collet chuck  
Collet chuck with ER25 collet for shanks from  $\varnothing 1.5$  to  $\varnothing 16$  mm (Other diameters between 1.5 and 16 mm available on request)



PRES-PMB



PRES-TE



PRES-ER25

### DISCOUNTS

Qty	1+	2+
Disc.	List	On request

Part number	Type	For shank diameter	Price each
PRES-PMB	Micrometric adjustment (0.02mm)	-	502,59 €
PRES-TE	Set of slot nuts for T profile slots	-	41,66 €
PRES-ER25-1.5	tool holder	1,5	450,30 €
PRES-ER25-2	tool holder	2	450,30 €
PRES-ER25-4	tool holder	4	450,30 €
PRES-ER25-6	tool holder	6	450,30 €
PRES-ER25-8	tool holder	8	450,30 €
PRES-ER25-10	tool holder	10	450,30 €
PRES-ER25-12	tool holder	12	450,30 €
PRES-ER25-14	tool holder	14	450,30 €
PRES-ER25-16	tool holder	16	450,30 €

Dimensions in mm