

## **Manual bench press**



PRES7HR


**700kg capacity**

### - Knee-joint press

- The maximum power is reached at the end of the stroke
- The travelling nut is prevented from turning
- Adjustable free height
- Screw stroke adjustment
- Quick and easy installation

## Uses

- This model is particularly robust and is normally used for the assembly of parts, simple bending tasks and various fastening operations



## DISCOUNTS

**DISCOUNTS**

<b>Qty</b>	1+	2+
<b>Disc.</b>	List	On request

Part number	Power (kg)	Free height HL (mm)	Stroke length (mm)	Goose neck depth (mm)	Weight (kg)	Price each
PRES-7-HR	700	35 - 260	40	95	25	955.42 €

---

*Dimensions in mm*

Tel. +33(0)4 37 496 496

cial2@hpceurope.com

WEB  
04/2021

**HPC**

## Our other products



Hexagonal shaft,  
Hexagonal shaft



Worm and wheel set,  
Non hardened steel



Needle roller double  
universal joint -  
Stainless steel, Heavy  
duty



Lip seal for panel,  
Door seal - Ø 2mm



90°ball and socket  
joints DIN71802, Steel



Articulated levelling  
foot, pressed base  
Ø50, 4000N



Accessory for  
adjustment slide-  
system, 20



Stainless steel  
spherical bearing,  
Stainless steel / PTFE



Roller guide,



Plastic spur gear,  
Machined plastic  
(delrin)



Reducing sleeve  
male/female,  
Hexagonal - steel



Articulated bracket for  
use with aluminium  
profile, With clamping  
ha...

## Complementary products



Manual workbench  
press, Force up to  
500kg



Manual workbench  
press, Force up to  
600kg



Flanged drill bushing,  
Steel



Flanged drill bushing,  
Steel