

Die spring ISO 10243




R Yellow: extra-heavy duty

- ISO yellow standard (ISO 10243)
- Extra-rigid spring
- For extra-heavy loads
- Trapezoidal wire
- Ends squared and ground
- Withstands shocks
- Tolerates shaking
- Easy to compress to solid height
- Material: chromium-vanadium steel



Advantages

- The trapezoidal wire permits optimum deflection whilst protecting against the risk of damage caused by overloading the spring.
- Hardness sufficient to allow heavy loads to be withstood.
- Heat resistant up to 230°C.
- Uniform spring performance.
- Uniform stiffness ratio
- Greater load accuracy for a given height.
- Reliable performance.
- Reduced risk of breakage.



Option

- Other sizes



DISCOUNTS

Qty	1+	6+	10+	20+	40+
Disc.	List	-15%	-20%	-25%	On request

Part number	Hole ØA (mm)	Rod ØB (mm)	Free length Lo (mm)	Load at 1 mm deflection (N)	Load table								Price each 1 to 5
					Optimum life (25% free length L ₀)		Long life (30% free length L ₀)		Max. working (35% free length L ₀)		Max. deflection		
					Load (N)	Deflection (mm)	Load (N)	Deflection (mm)	Load (N)	Deflection (mm)	Load (N)	Deflection (mm)	
R206104	10,0	5,0	25,0	36,8	138,0	3,8	156,4	4,3	184,0	5,0	228,2	6,2	3,34 €
R206106	10,0	5,0	38,0	23,7	135,1	5,7	153,1	6,5	180,1	7,6	225,2	9,5	4,06 €
R206108	10,0	5,0	51,0	16,5	126,2	7,7	143,1	8,7	168,3	10,2	214,5	13,0	4,84 €
R206112	10,0	5,0	76,0	10,9	124,3	11,4	140,8	12,9	165,7	15,2	207,1	19,0	5,31 €
R206204	12,5	6,3	25,0	58,5	219,4	3,8	248,6	4,3	292,5	5,0	362,7	6,2	4,06 €
R206206	12,5	6,3	38,0	36,0	205,2	5,7	232,6	6,5	273,6	7,6	342,0	9,5	4,84 €
R206208	12,5	6,3	51,0	26,2	200,4	7,7	227,2	8,7	267,2	10,2	340,6	13,0	5,52 €
R206212	12,5	6,3	76,0	17,1	194,9	11,4	220,9	12,9	259,9	15,2	324,9	19,0	6,65 €
R206248	12,5	6,3	305,0	4,3	196,7	45,8	223,0	51,9	262,3	61,0	326,8	76,0	26,83 €
R206305	16,0	8,0	32,0	89,0	427,2	4,8	484,2	5,4	569,6	6,4	712,0	8,0	5,14 €
R206307	16,0	8,0	44,0	60,9	401,9	6,6	455,5	7,5	535,9	8,8	669,9	11,0	5,91 €
R206310	16,0	8,0	64,0	41,2	395,5	9,6	448,3	10,9	527,4	12,8	659,2	16,0	6,90 €
R206314	16,0	8,0	89,0	29,5	393,8	13,4	446,3	15,1	525,1	17,8	649,0	22,0	7,68 €
R206348	16,0	8,0	305,0	8,4	384,3	45,8	435,5	51,9	512,4	61,0	638,4	76,0	28,03 €
R206404	20,0	10,0	25,0	293,0	1098,8	3,8	1245,3	4,3	1465,0	5,0	1816,6	6,2	5,70 €
R206405	20,0	10,0	32,0	224,0	1075,2	4,8	1218,6	5,4	1433,6	6,4	1792,0	8,0	6,34 €

Dimensions in mm

Part number	Hole ØA (mm)	Rod ØB (mm)	Free length Lo (mm)	Load at 1 mm deflection (N)	Load table								Price each 1 to 5
					Optimum life (25% free length Lo)		Long life (30% free length Lo)		Max. working (35% free length Lo)		Max. deflection		
					Load (N)	Deflection (mm)	Load (N)	Deflection (mm)	Load (N)	Deflection (mm)	Load (N)	Deflection (mm)	
R206406	20,0	10,0	38,0	177,0	1008,9	5,7	1143,4	6,5	1345,2	7,6	1681,5	9,5	6,65 €
R206407	20,0	10,0	44,0	149,0	983,4	6,6	1114,5	7,5	1311,2	8,8	1639,0	11,0	6,38 €
R206408	20,0	10,0	51,0	128,0	979,2	7,7	1109,8	8,7	1305,6	10,2	1664,0	13,0	7,68 €
R206410	20,0	10,0	64,0	99,0	950,4	9,6	1077,1	10,9	1267,2	12,8	1584,0	16,0	8,28 €
R206412	20,0	10,0	76,0	81,7	931,4	11,4	1055,6	12,9	1241,8	15,2	1552,3	19,0	8,87 €
R206414	20,0	10,0	89,0	69,5	927,8	13,4	1051,5	15,1	1237,1	17,8	1529,0	22,0	10,25 €
R206416	20,0	10,0	102,0	60,6	927,2	15,3	1050,8	17,3	1236,2	20,4	1575,6	26,0	10,04 €
R206418	20,0	10,0	115,0	53,0	914,3	17,3	1036,2	19,6	1219,0	23,0	1537,0	29,0	11,11 €
R206420	20,0	10,0	127,0	47,5	904,9	19,1	1025,5	21,6	1206,5	25,4	1520,0	32,0	12,22 €
R206422	20,0	10,0	139,0	43,0	896,9	20,9	1016,1	23,6	1195,4	27,8	1505,0	35,0	13,35 €
R206424	20,0	10,0	152,0	39,0	889,2	22,8	1007,8	25,8	1185,6	30,4	1482,0	38,0	16,22 €
R206448	20,0	10,0	305,0	21,2	969,9	45,8	1099,2	51,9	1293,2	61,0	1611,2	76,0	38,81 €
R206505	25,0	12,5	32,0	374,4	1797,1	4,8	2036,7	5,4	2396,2	6,4	2995,2	8,0	6,26 €
R206506	25,0	12,5	38,0	346,0	1972,2	5,7	2235,2	6,5	2629,6	7,6	3287,0	9,5	7,68 €
R206507	25,0	12,5	44,0	244,0	1610,4	6,6	1825,1	7,5	2147,2	8,8	2684,0	11,0	8,28 €
R206508	25,0	12,5	51,0	207,5	1587,4	7,7	1799,0	8,7	2116,5	10,2	2697,5	13,0	9,18 €
R206510	25,0	12,5	64,0	161,0	1545,6	9,6	1751,7	10,9	2060,8	12,8	2576,0	16,0	9,01 €
R206512	25,0	12,5	76,0	130,8	1491,1	11,4	1689,9	12,9	1988,2	15,2	2485,2	19,0	10,90 €
R206514	25,0	12,5	89,0	110,5	1475,2	13,4	1671,9	15,1	1966,9	17,8	2431,0	22,0	11,11 €
R206516	25,0	12,5	102,0	96,3	1473,4	15,3	1669,8	17,3	1964,5	20,4	2503,8	26,0	12,22 €
R206518	25,0	12,5	115,0	85,7	1478,3	17,3	1675,4	19,6	1971,1	23,0	2485,3	29,0	13,64 €
R206520	25,0	12,5	127,0	76,3	1453,5	19,1	1647,3	21,6	1938,0	25,4	2441,6	32,0	16,39 €
R206524	25,0	12,5	152,0	63,5	1447,8	22,8	1640,8	25,8	1930,4	30,4	2413,0	38,0	17,17 €
R206528	25,0	12,5	178,0	53,9	1439,1	26,7	1631,0	30,3	1918,8	35,6	2371,6	44,0	19,53 €
R206532	25,0	12,5	203,0	47,0	1431,2	30,5	1622,0	34,5	1908,2	40,6	2397,0	51,0	21,85 €
R206548	25,0	12,5	305,0	30,9	1413,7	45,8	1602,2	51,9	1884,9	61,0	2348,4	76,0	49,04 €
R206606	32,0	16,0	38,0	528,2	3010,7	5,7	3412,2	6,5	4014,3	7,6	5017,9	9,5	9,22 €
R206607	32,0	16,0	44,0	424,4	2801,0	6,6	3174,5	7,5	3734,7	8,8	4668,4	11,0	10,90 €
R206608	32,0	16,0	51,0	353,0	2700,5	7,7	3060,5	8,7	3600,6	10,2	4589,0	13,0	12,01 €
R206610	32,0	16,0	64,0	269,2	2584,3	9,6	2928,9	10,9	3445,8	12,8	4307,2	16,0	13,35 €
R206612	32,0	16,0	76,0	218,5	2490,9	11,4	2823,0	12,9	3321,2	15,2	4151,9	19,0	15,27 €
R206614	32,0	16,0	89,0	180,3	2407,0	13,4	2727,9	15,1	3209,3	17,8	3966,6	22,0	15,66 €
R206616	32,0	16,0	102,0	155,0	2371,5	15,3	2687,7	17,3	3162,0	20,4	4030,0	26,0	19,06 €
R206618	32,0	16,0	115,0	140,0	2415,0	17,3	2737,0	19,6	3220,0	23,0	4060,0	29,0	19,53 €
R206620	32,0	16,0	127,0	124,0	2362,2	19,1	2677,2	21,6	3149,6	25,4	3968,0	32,0	21,63 €
R206624	32,0	16,0	152,0	102,0	2325,6	22,8	2635,7	25,8	3100,8	30,4	3876,0	38,0	25,71 €
R206628	32,0	16,0	178,0	88,2	2354,9	26,7	2668,9	30,3	3139,9	35,6	3880,8	44,0	29,58 €
R206632	32,0	16,0	203,0	76,0	2314,2	30,5	2622,8	34,5	3085,6	40,6	3876,0	51,0	33,44 €
R206640	32,0	16,0	254,0	60,8	2316,5	38,1	2625,3	43,2	3088,6	50,8	3891,2	64,0	41,77 €
R206708	40,0	20,0	51,0	628,0	4804,2	7,7	5444,8	8,7	6405,6	10,2	8164,0	13,0	14,19 €
R206712	40,0	20,0	76,0	379,0	4320,6	11,4	4986,7	12,9	5760,8	15,2	7201,0	19,0	19,96 €
R206716	40,0	20,0	102,0	281,0	4299,3	15,3	4872,5	17,3	5732,4	20,4	7306,0	26,0	27,46 €
R206720	40,0	20,0	127,0	221,0	4210,1	19,1	4771,4	21,6	5613,4	25,4	7072,0	32,0	35,89 €
R206732	40,0	20,0	203,0	132,0	4019,4	30,5	4555,3	34,5	5359,2	40,6	6732,0	51,0	47,70 €
R206748	40,0	20,0	305,0	87,8	4016,9	45,8	4552,4	51,9	5355,8	61,0	6672,8	76,0	70,94 €
R206810	50,0	25,0	64,0	709,0	6806,4	9,6	7713,9	10,9	9075,2	12,8	11344,0	16,0	28,76 €
R206814	50,0	25,0	89,0	475,0	6541,3	13,4	7186,8	15,1	8455,0	17,8	10450,0	22,0	38,39 €
R206818	50,0	25,0	115,0	352,0	6072,0	17,3	6881,6	19,6	8096,0	23,0	10208,0	29,0	47,70 €
R206824	50,0	25,0	152,0	239,0	5449,2	22,8	6175,8	25,8	7265,6	30,4	9082,0	38,0	57,02 €
R206840	50,0	25,0	254,0	153,0	5829,3	38,1	6606,5	43,2	7772,4	50,8	9792,0	64,0	92,33 €

Dimensions in mm

Our other products




CHTRP

Single and dual output gearboxes, Up to 28,8 Nm



SBF

Sealed flange bearing unit for Food Industry, cover



RPP

Connecting plate for RPP type timing belts, RRP5




LRR22

Small dimension latch with locking system, Aluminium



T5M T10M

T type timing belt per metre, T10 Steel cored polyurethane



M1

Worm and wheel set, Machined plastic (delrin)



GMK17_R

Round guide, Round guide for conical profile



NCT_AT

Variable angle connector, Variable angle



UTKpwrr

V shaped channel UtiliTrak®, V rail



NCT

Square tube connector, Fixed



DOMI30

Accessories, Plate



PTMR

Telescopic furniture foot, threaded stud

Complementary products



R203

Die spring ISO10243, Light



R204

Die spring ISO10243, Average



CDGamme

Compression spring DIN2095, DIN 2095



R205

Die spring ISO10243, Heavy