

Manual bench press




PRES7HR

700kg capacity

- **Knee-joint press**
- The maximum power is reached at the end of the stroke
- The travelling nut is prevented from turning
- Adjustable free height
- Screw stroke adjustment
- Quick and easy installation

Uses

- This model is particularly robust and is normally used for the assembly of parts, simple bending tasks and various fastening operations



DISCOUNTS

Qty	1+	2+
Disc.	List	On request

Part number	Power (kg)	Free height HL (mm)	Stroke length (mm)	Goose neck depth (mm)	Weight (kg)	Price each
PRES-7HR	700	35 - 260	40	95	25	955,42 €

Dimensions in mm

Our other products



GPB5S

Threaded spherical knob, Stainless steel 304



RBNpl

Swivel castor with plate, Steel - rubber



PLM-SC

Magnetic stud with central countersunk hole, With milled bore




HK

Manual locking clamp, Manual locking clamp LWL



CHINV

Invisible hinge, Invisible - Opening up to 90°



RPP8

RPP heavy duty timing belt, RPP8



CFUURSS

Cam follower stainless steel, Standard - stainless steel



AZY_SS

Stainless steel cylindrical elastomount, Stainless steel




LRR-53

Spring loaded latch, Spring return latch -



VDSCB

Sliding lock adjustment system, VDSCB



PRF PSP PR

Dual purpose strip and cover for



PR40

Articulated foot Ø50, Ø 50

Complementary products



PRESSHR

Manual workbench press, Force up to 500kg



PRES4HR

Manual workbench press, Force up to 600kg



CDP

Flanged drill bushing, Steel



CDPC

Flanged drill bushing, Steel