

Standard fastener

MiniTec

PRF  
FIXSTD**Profile assembly**




- Suitable for loads up to 18000N
- Can be used to securely join all profile types
- Forms very efficient anti-twist joint
- Materials:  
M8x50mm CHC screw: electroplated steel  
Locking plate: electroplated steel

**Uses**

- For heavy or vibrating loads

**Assembly**

- Drill a stepped hole (Ø9, Ø15) at the required position
- Slide the screw locking plate in the slot
- Pass the end of the screw through the first profile (1), the locking plate and then into the central hole of the second profile (2) which was previously tapped (M8 x 25mm) and tighten.

**DISCOUNTS**

Qty	1+	50+	100+
Disc.	List	-5%	On request

Part number	Load (N)	For profile	Tightening torque (Nm)	Weight (kg)	Stock*	Price each 1 to 49
PRF-FIX-STD	18000	All types of PRF profile	20	0,03	✓	2,10 €

\*Depending on availability - Dimensions in mm

## Our other products



RPP14

RPP heavy duty timing belt, RPP14



ERC

Quick fitting cable terminal, Eye version



PSP

Support profile, Panel support



SUA4\_L

Chain link, Steel



ACL

Joints for aluminium profile, Variable angle hinge



CHAL3

Piano hinge, Steel



RFK28B

Hypoid gearbox - Stainless steel, up to 130 Nm



T5M T10M

T type timing belt per metre, T10 Steel cored polyurethane



LVT

Miniature motorised actuator 2A, 2 ampers



MET

Cylindrical sintered bronze bush, Self-lubricating sintered bronze



GLB

Small 6 lobe female handle, Technopolymer - Stainless steel



INS150

Self tapping insert with collar-coarse thread, With collar-coarse t...

## Complementary products



PRF1932

Standard aluminium profile, 19 x 32 mm




PRF4545

Standard stainless steel profile, 45 x 45 mm - mm



PRF\_FIX\_UNI

Universal fastener for aluminium profile, Universal



PRF4545r90

Standard aluminium profile, 45 x 45 mm - R90°