

**Profile assembly**



- Suitable for loads up to 18000N
- Can be used to securely join all profile types
- Forms very efficient anti-twist joint
- Materials:  
M8x50mm CHC screw: electroplated steel  
Locking plate: electroplated steel

**Uses**

- For heavy or vibrating loads

**Assembly**

- Drill a stepped hole ( $\varnothing 9$ ,  $\varnothing 15$ ) at the required position
- Slide the screw locking plate in the slot
- Pass the end of the screw through the first profile (1), the locking plate and then into the central hole of the second profile (2) which was previously tapped ( $M8 \times 25\text{mm}$ ) and tighten.

**DISCOUNTS**

Qty	1+	50+	100+
Disc.	List	-5%	On request

Part number	Load (N)	For profile	Tightening torque (Nm)	Weight (kg)	Stock*	Price each 1 to 49
PRF-FIX-STD	18000	All types of PRF profile	20	0,03	✓	2,10 €

\*Depending on availability - Dimensions in mm

## Our other products



PRF19\_E

Bracket for aluminium profile, PRF19 to PRF45



NJM

Multiple junction clamp, Multiple



VHTM

Hexagonal headed screw Hygienic Design®, Stainless steel



Q1

Self-aligning radial ball bearing, Steel



CFF\_SS

Female rod ends DIN ISO12240-4, Stainless steel / bronze - Economy r...



PTCR

Adjustable furniture foot, square tube



DOMI120

Accessories, Fixing kit



PTRSS

Idler chain sprocket, For hostile environments




ESCON

Speed controller 5A accessories, Kit of 4 cables for DC motor




BOXKK

Boxed set of DIN6885A keys, Boxed set - Steel or



PRL

Wear strip for slat pot chain, L profile to be clipped



QNJ

Single row cylindrical roller bearing, Single flange on inner ring

## Complementary products



PRF1932

Standard aluminium profile, 19 x 32 mm




PRF4545

Standard stainless steel profile, 45 x 45 mm



PRF\_FIX\_UNI

Universal fastener for aluminium profile, Universal



PRF4545r90

Standard aluminium profile, 45 x 45 mm - R90°