

# Floway2® roller track and basic support

## RAG- FLOW2

### Principal of operation




- The Floway2® roller track allows storage systems to be created for plastic boxes or cardboard cartons

### Support



- For easy installation of roller tracks
- Suitable for use in gravity feed conveyors
- Material:  
Electro-galvanised steel

### Assembly

- Slide the roller track into the end support
- Position the complete assembly on the supporting structure
- Track can be locked in place using a screw (tapped hole to be drilled on site)



Basic support



Support with stop



# Floway2® roller track and basic support


For transporting and storage

## RAG-FLOW2

- High density polyethylene roller
- Chromed steel guide (no deformation under load)
- Rollers rotate on steel axes
- Colour: Black

### Special Features

- The possibility of being able to stagger the position of the rails increases the performance of the system



RAG-FLOW2-A

RAG-FLOW2-B

### DISCOUNTS Roller track DISCOUNTS Basic support

Qté	1+	5+	10+	Qté	1+	50+	100+
Disc.	Prix	-5%	On request	Disc.	Prix	-5%	On request

#### Roller track

Part number	P1	P2	Length L	N° of rollers	Max load per roller (kg)	Stock*	Price each 1 à 4
RAG-FLOW2-1000	35	41	1000 ±1	980	34	10	✓ 24,51 €
RAG-FLOW2-2000	35	33	2046 ±1	2016	70	10	✓ 40,33 €

#### Basic support

Part number	Description	Thickness	Weight (g)	Stock*	Price each 1 à 49
RAG-FLOW2-A	Basic support	2	124	✓	8,16 €
RAG-FLOW2-B	Support with stop	2	141	-	8,16 €

\*Subject to available stocks - Dimensions in mm

## Our other products



Ball transfer unit push fit, Light



Motor-gearbox 12V and 24V DC, from 4 to 9 Nm



Threaded blocking clamp, Threaded locking clamp



Parallel axis helical gear, Steel 20NCD2



Masterplate® glueable insert rectangular, rectangular with



Single stainless steel universal joint, Low duty



Toggle latches, With padlock-holder



Right angled gearbox, double output shafts, up to 4.4 Nm



Box set of self tapping inserts, Boxed set - For wood



Guide roller for plate chain return, Without ball bearing



Clevis components, short version, Steel - Short range



Spur gear coaxial gearbox, from 0.13 to 0.49 Nm - Inline

## Complementary products



Floway2® Roller track accessory, Roller track support



Roller guide,



Cylindrical brush track, For gentle conveying and handling